

SICLIMAT™ X

## IOPRO4/8P/I multi-port adapter

## IOPRO 4/8P/I

---

Multi-port adapters are plugged into the SICLIMAT X-OS to provide additional serial ports. The multi-port adapters are available with 4 or 8 serial ports. There are versions for PCI slots and for ISA (AT) slots.

### Use

---

The multi-port adapters increase the number of serial ports available with the SICLIMAT X-OS, e.g. for the connection of a printer or a serial radio-controlled clock. The multi-port adapters can be connected to single and multi-user systems (subject to the number of available slots).

### Function

---

- Increases the number of serial ports normally available with the SICLIMAT X-OS
- Provides 4 or 8 additional serial ports per slot
- Adapts the PCI bus or ISA bus
- Adapts the 4 RJ45 connectors on the front panel of the multi-port adapter with 4 serial ports to give 4 x DB25 male connectors (4 cables)
- Adapts the connector on the front panel of the multi-port adapter with 8 serial ports to give 8 x DB25 female connectors (box).

**Prerequisites**


- Free PCI or ISA slot in the X-OS
- SICLIMAT X Version V3.1

**Ordering**

When ordering, please specify the quantity, product name and type code.

Type	Order No.	Specification No.
<b>IOPRO4P</b>	<b>6FL4101-3NA12</b>	<b>15/43062</b>
<b>IOPRO8P</b>	<b>6FL4101-3NA13</b>	<b>15/43063</b>
<b>IOPRO4I</b>	<b>6FL4101-3NA14</b>	<b>15/43064</b>
<b>IOPRO8I</b>	<b>6FL4101-3NA15</b>	<b>15/43065</b>

**Example**



**Technical data**

	Types	IOPRO4P, IOPRO8P, IOPRO4I, IOPRO8I
Data	Card dimensions	Multi-port adapters with 4 serial ports: ½ length Multi-port adapters with 8 serial ports: ¾ length
	Driver support	SCO
Connections/interfaces	Transmission speed	Up to 460.8 kbit/s asynchronous
	IOPRO4P, IOPRO4I	Multi-port adapters with 4 serial ports: 4 x RJ45 RJ45 – DB25 converters (pack of 4), male
	IOPRO8P, IOPRO8I	Multi-port adapters with 8 serial ports: board connector, 8-port Dbox, DB25, female
	Internal PC bus	IOPRO4P, IOPRO8P: PCI IOPRO4I, IOPRO8I: ISA (AT)
	Signal cables	FG, SG, TXD, RXD, RTS, CTS
	Cables:	Cable lengths:
	RJ45 – DB25 converter	4 x 1.5m
	8-port Dbox DB25	1m
Product safety	Conformity	Meets the requirements for CE marking