



RE8ST, RE8STCO

Sinteso™
Cerberus™ PRO

Testfire 1001-101 RT test kit



Testfire 2001-101 RTCO test kit

- **The test kit RE8ST tester kit is composed of:**
 - 1 Testfire 1001-101 tester
 - 1 RE8-S smoke capsule
 - 2 batteries
 - 1 charger (incl. 12V connection cable)
 - 2 mains cables (110 / 120-220 / 240 VAC)
 - 1 USB cable
- **The test kit RE8STCO tester kit is composed of:**
 - 1 Testfire 2001-101 tester
 - 1 RE8-S smoke capsule
 - 1 RE8-CO CO capsule
 - 2 batteries
 - 1 charger (incl. 12V connection cable)
 - 2 mains cables (110 / 120-220 / 240 VAC)
 - 1 USB cable
- **Battery powered**
- **Rapid activation**
- **Lightweight and simple to use**
- **Universal: suitable for use on most detectors**
- **Detectors can also be tested in high rooms or at angles by using telescopic rods and adaptor.**



Forbidden in electrical switching stations or areas where there is a danger of explosion!

Comply with the operating instructions on the detector tester.

RE8ST: Kit and accessories



- Testfire tester (1 piece): part of the kit



- RE8-S smoke capsule (1 piece): part of the kit



- Battery (2 pieces): part of the kit



- Charger (1 piece) : part of the kit



- Heat detector adaptor (accessory) for telescopic rods FDUM29x:
must be ordered separately

RE8ST: Kit and accessories



- Testfire tester (1 piece): part of the kit



- RE8-S smoke capsule (1 piece): part of the kit



- RE8-CO CO capsule (1 piece): part of the kit



- Battery (2 pieces): part of the kit



- Charger (1 piece) : part of the kit



- Heat detector adaptor (accessory) for telescopic rods FDUM29x:
must be ordered separately

Characteristics

- yellow plastic tubes in light and robust execution (non-conductive material)
- plastic sockets and slide bearings provide for easy sliding of the tubes
- quick spring-type locking mechanisms and continuous length adjustment
- The tubes can be extended to their maximum length and are protected against further extension by a stop bolt.
- Further extension of the telescopic rods is not possible.


FDUM291

- light telescopic rod for all applications, for room heights up to 5.5 m
- latch catch for continuous length adjustment
- three-part telescopic with tri-oval tubes as practical grip
- distortion of the tubes is not possible
- weight 1.2 kg without attached tool

FDUM292

- long, robust telescopic rod for room heights up to 8 m
- handle catch for continuous length adjustment
- stable, four-part telescopic with round tubes
- weight 3.4 kg without attached tool


FDUM291



FDUM291
L= drawn in length 1.6 m
L= drawn out length 4.2 m

FDUM292
L= drawn in length 2.1 m
L= drawn out length 7.3 m


FDUM292




Beware of falling objects when working with a telescopic rod. Hardhat required.

Technical data

RE8ST & RE8STCO	Recharge time	1 hour for each battery baton
	Power supply	Vehicle: 12 VDC; Main: 110 / 120-220 /240 VAC
	Humidity (no condensation permitted)	≤95 %
	Operating / storage temperature	0... +35 °C / -25... +70 °C

	RE7T-B1	Detector testers (No Climb Products Limited), Edison House, 163 Dixons Hill Road, Welham Green, Hertfordshire, AL9 7JE United Kingdom Technical data: see doc. A6V10252901
	RE7T-B1 Solo770 Battery for RE7T	
2014/30/EU (EMC): EN 55011 / EN 61000-4-2 / EN 61000-4-3 ; 2014/35/EU (LVD): EN 62133 ; 2011/65/EU (RoHS): EN 50581		
The EU Declaration of conformity (DOC), which is obtainable via Detector testers (No Climb Products Limited)		
DoC No.: Solo 461 (Solo 460-770-727) New Framework EU Declaration of Conformity-M		

	RE7T-C1	Detector testers (No Climb Products Limited), Edison House, 163 Dixons Hill Road, Welham Green, Hertfordshire, AL9 7JE United Kingdom Technical data: see doc. A6V10252901
	RE7T-C1 Solo727 Charger for RET7.	
2014/30/EU (EMC): EN 55014-1 / EN 55014-2 ; EN 61000-3-2 / EN 61000-3-3 ; 2014/35/EU (LVD): EN 60335-1 / EN 60335-2-29 ; 2011/65/EU (RoHS): EN 50581		
The EU Declaration of conformity (DoC), which is obtainable via Detector testers (No Climb Products Limited)		
DoC No.: Solo 461 (Solo 460-770-727) New Framework EU Declaration of Conformity-M		

Details for ordering

	Type	Part no.	Designation	Weight
Detector tester	RE8ST	S54370-S23-A1	Testfire 1001-101 RT test kit	3.470 kg
	RE8STCO	S54370-S24-A1	Testfire 2001-101 RTCO test kit	3.750 kg
Capsules	RE8-S	S54370-N25-A1	TS3 smoke capsules (6 pieces)	0.079 kg
	RE8-CO	S54370-N22-A1	TS3 CO capsules (6 pieces)	0.077 kg
Accessory	RE7T-A	S54370-N4-A1	Solo719 Adaptor for FDUM29x	0.260 kg
Spare parts	RE7T-B1	S54370-N7-A1	Solo770 Battery for RE7T	1.090 kg
	RE7T-C1	S54370-N8-A1	Solo727 Charger for RE7T	1.210 kg
Telescopic rods	FDUM291	A5Q00004996	Telescopic rod three-part telescopic with tri-oval tubes (1.6 m / 4.2 m)	1.960 kg
Spare parts	-	A5Q00009787	Lever with screw and nut (Handle catch)	0.023 kg
	-	A5Q00009786	Adapter with lever, screw and nut incl. attachment and bushing screw	0.088 kg
	-	A5Q00009788	Small flap with screw and nut (Latch catch)	0.015 kg
	-	A5Q00009789	Large flap with screw and nut (Latch catch)	0.016 kg
	FDUM292	A5Q00004997	Telescopic rod four-part telescopic with round tubes (2.1 m / 7.3 m)	4.480 kg
Spare parts	-	A5Q00009787	Lever with screw and nut (Handle catch)	0.020 kg
	-	A5Q00009786	Adapter with lever, screw and nut incl. attachment and bushing screw	0.088 kg

Siemens Schweiz AG
Building Technologies Division
International Headquarters
CPS Fire Safety
Theilerstrasse 1a
CH-6300 Zug
Tel. +41 58 - 724 24 24
www.siemens.com/buildingtechnologies

©2013 Copyright by
Siemens Schweiz AG
Data and design subject to change without notice.
Supply subject to availability.