

SIEMENS

Building Technologies Division

CPS Fire Safety



Sinteso - Overview Technical Documentation (MP6)

This document contains an overview of Sinteso documentation provided by FS HQ. This document and all listed documents will be maintained by FS HQ. This document as well as all listed documents inside this document are stored in the STEP Portal. Below please find the web address to open the global BT home page:

<https://workspace.sbt.siemens.com/content/00001123/default.aspx>

Enter in the field "Key word" (with asterisk):

A6Vxxxxxxx or

XXXX(Document number) or

FC20XX (Key word)

Name	Description	Doc-number
FS20 Fire detection system	Contents	009080
FD20 Detector system	Contents	008723
FD20 Fire detectors overview		
FD20 Detector system	Equipment overview	008164
FD20 Detector system	List of compatibility	008331
FD20 Point detectors		
FDOOT221, FDO221, FDT221, Automatic fire detectors	Data sheet	007850
FDOOT241-A3, FDOOT241-A4, FDOOT241-A5, FDOOT241-A9, FDOOT241-8 Multi-sensor fire detector for gradual modernization with ASAtechnology™	Data sheet	008141
FDOOT241-9, FDOOT241-A, FDO241, FDT241 Automatic fire detectors	Data sheet	007005
FDOOT221, FDOOT241-A3, FDOOT241-A4, FDOOT241-A5, FDOOT241-8, FDOOT241-9, FDOOT241-A9, FDO241, FDO221, FDT241, FDT221 Automatic fire detectors	Technical manual	007004
FDO., FDOOT..., FDT..., FDB..., FDCW241 Colored detector, base, and base attachment	Data sheet	009409
FDOOT241-A3, FDOOT241-A4, FDOOT241-A5, FDOOT241-A9, FDOOT241-8 Modernizing fire detection installations with multiple protocol detectors	Technical manual	A6V10323158
FD20 Special detectors		
FDA221, FDA241 Aspirating Smoke Detector	Data sheet	A6V10331032
FDOOT271, FDCW241, FDM273, FDM275 SWING radio fire system	Data sheet	A6V10271323
FDA221, FDA241 Aspirating Smoke Detector	Technical manual	A6V10334410
FDM273 Radio manual call point	Technical manual	A6V10347733
FDM273 Radio manual call point	Installation	A6V10347888
FDM275 Radio manual call point	Technical manual	A6V10401120
FDM275 Radio manual call point	Installation	A6V10401114
FDOOT271 Radio fire detector	Technical manual	A6V10227635
ASD Pipe System	Projection, Installation	A6V10334435
FDA241, FDA221 Aspirating Smoke Detector	Installation	A6V10345654
FDOOT271, FDB271 Radio fire detector, detector base	Installation	A6V10227637
FXS2051 ASD configuration tool	Installation, Operation, Configuration	A6V10332759
FDOOTC241 Neural fire detector	Data sheet	A6V10217810
FDOOTC241 Neural fire detector	Technical manual	A6V10209291
FDF221-9, FDF241-9 Infrared flame detectors	Data sheet	007012
FDF221-9, FDF241-9, Flame detector	Technical manual	007011
FDF221-9, FDF241-9, Flame detector	Installation	A6V10299713
FDF221-9, FDF241-9, Flame detector	Commissioning	A6V10299652
FDFB291 Base for flame detector	Installation	007984
FDF221-9; FDF241-9, Flame detector	Installation	008121
FDL241-9, Linear smoke detector	Data sheet	007017
FDL241-9, Linear smoke detector	Technical manual	007016
FDL241-9 Linear smoke detector FDLB291 Detector base DLR119x Reflector	Installation	008186
FDF221-9, FDF241-9 Flame detector FDL241-9 Linear smoke detector	Commissioning	008337
FDL241-9 Linear smoke detector FDLU291 Adjustment tester	Commissioning	008254
VLF-250, VLF-500 LaserFocus	Data sheet	A6V10221433

FDBZ292, Air sampling detection kit	Data sheet	009728
FDBZ292 Air sampling smoke detection kit	Installation	009726
FDBZ290 Air sampling smoke detection kit	Data sheet	A6V10405166
FDBZ290 Air sampling smoke detection kit	Technical manual	A6V10409732
DOW1171, DBW1171 Radio smoke detector, Base	Installation	A6V10336739
FD20 Manual Call Points		
FDM221, FDM223, FDM224 Manual call points addressable	Data sheet	007001
FDM223, FDM224, FDM223H, FDM224H Manual call point	Technical manual	007002
FDMH291 Housing, FDME221, MTE320C, DMA1101, DMA1131, DMA1151 Call point unit	Installation	007904
FDMH293-x, FDMH297-R Housing for manual call point FDME223, FDME224 Switching unit	Installation	007905
FDM223H, FDM224H Manual call points "Heavy duty"	Data sheet	008345
FDMH292-R Back box for manual call point 'Heavy Duty'	Installation	008615
FDM225, FDM226 Manual call point	Data sheet	009023
FDM221, FDM225, FDM226 Manual call point	Technical manual	009757
FDM221, FDM225, FDM226 Manual call point	Installation	009371
SMF6120 Radio base, SMF121 Manual call point	Installation	A6V10200368
FDM231-RP, FDM231-RP(F) Manual call points	Data sheet	A6V10404251
FDM231-RP, FDM231-RP(F) Manual call points	Technical manual	A6V10404679
FDM231-RP, FDM231-RP(F) Manual call points	Installation	A6V10404670
FDM243H Manual call point	Data sheet	A6V10356927
FDM243H Manual call point	Technical manual	A6V10374021
FDM243H Manual call point	Installation	A6V10374023
FDM233, FDM234 Manual call point	Data sheet	A6V10356826
FDM233, FDM234 Manual call point	Technical manual	A6V10374017
FDM233, FDM234 Manual call point	Installation	A6V10374019
FD20 Line devices		
FDCI221, FDCIO221 Input module, input/output module	Data sheet	A6V10202196
FDCI221, FDCIO221 Input module, input/output module	Technical manual	A6V10211122
FDCI222, FDCIO222, FDCIO224 Input module, input/output modules	Data sheet	007024
FDCI222, FDCIO222, FDCIO224 Input module, input/output module	Technical manual	007023
FDCI222 Input module, FDCH221 Housing	Installation	008175
FDCIO222, FDCIO224 Input/output module, FDCH221 Housing	Installation	008176
FDCW241 Radio gateway	Technical manual	A6V10227639
FDCW241 Radio gateway	Installation	A6V10227641
SWING Radio fire detection system	Planning	A6V10227631
FDCIO223 (ES ≤ 45) Transponder	Data sheet	009168
FDCIO223 Input / output module (transponder) Valid for product version ES ≤ 45	Technical manual	009122
FDCIO223 Input/output module (Transponder), FDCH221 Housing	Installation	009124
FDCL221 Line separator	Data sheet	007065
FDCL221 Line separator	Technical manual	007063
FDCL221 Line separator	Installation	008025
FDCL221-M Multi line separator module	Data sheet	A6V10230308
FDCL221-M Multi line separator module	Technical manual	A6V10224006
FDCL221-M Multi line separator module, FDCH221 Housing	Installation	A6V10224008
FDCW221 / DOW1171 / SMF121 SMF6120 (repair/replacement) Sinteso™ Radio fire detection system	Data sheet	010087
FDCW221, DOW1171, SMF121, SMF6120 Radio gateway, radio smoke detector, manual call point, radio base	Technical manual	009865

FDCW221 Radio gateway	Installation	A6V10336734
FDCI223 Zone module, external powered	Data sheet	A6V10402141
FDCI223 Zone module, external powered	Technical manual	A6V10414906
FDCI223 Zone module, external powered, FDCH221 Housing	Installation	A6V10414908
FD20 Alarm devices		
FDSB221, FDSB229 Sounder interbase, Sounder interbase with supplementary optical indication	Data sheet	A6V10277376
FDSB221 Sounder interbase, FDSB229 Sounder beacon interbase	Technical manual	A6V10320090
FDSB221 Sounder interbase, FDSB229 Sounder beacon interbase	Installation	A6V10320092
FDSB291, FDSB292, FDS221-R, FDS221-W Sounder bases, Alarm sounders	Data sheet	007026
FDS221 Alarm Sounder	Technical manual	008109
FDS221 Alarm Sounder	Installation	008168
FDSB291 Sounder base	Technical manual	007025
FDSB292 Sounder base	Technical manual	009769
FDSB291, FDSB292 Sounder base	Installation	008114
FDS229-R, FDS229-A Alarm sounder beacon	Data sheet	A6V10067771
FDS229 Alarm sounder with supplementary optical indication	Technical manual	010095
FDS229 Alarm sounder with supplementary optical indication	Installation	010096
FDAI91, FDAI92, FDAI93 Alarm indicators	Data sheet	A6V10276520
FDAI91, FDAI92, FDAI93, AI330, DCA1191, DJZ1193 Alarm indicators, adapter frame, surface-mounted housing, indicator housing incl. washer	Installation	A6V10257736
FDCAI221 Addressable alarm indicator	Data sheet	A6V10244934
FDCAI221 Addressable alarm indicator	Technical manual	A6V10258110
FDCAI221 Addressable alarm indicator, AI330 additional frame	Installation	A6V10258105
AI91C, AI92C Alarm indicators, AI330 adapter frame	Installation	A6V10260484
FD20 Detector bases and options		
FDB22x, FDB20x, FDB2x1-AA, DBZ1190-Ax, FDBZ295, FDBZ291, DBZ1193A, FDBH291, FDBZ29x, FDB2x1, FDB29x, FDUD290, DBZ1194, FDBZ294, FDZ291 Detector base and accessories	Data sheet	007775
FDB20x/FDB201-AA, FDB22x/FDB221-AA Detector base, FDB291Base attachment, FDBZ291 Designation plate, FDX291 Dummy detector, FDBZ297 Detector base seal	Installation	A6V10208546
FDB293 Base attachment humid, DBZ1193A Detector designation plate, DBZ1194 Protective cage, FDBZ294 EMC-protective cage	Installation	A6V10208550
FDBZ293 Detector locking device	Installation	A6V10208552
FDBH291 Detector heating	Installation	008115
FDZ291 Detector dust cap	Installation	008117
FDBZ295 Sealing element	Installation	A6V10208532
FDFB291 Base for flame detector	Installation	A6V10299682
FDB295 Base attachment wet, DBZ1193A Detector designation plate, DBZ1194 Protective cage, FDBZ294 EMC-protective cage	Installation	A6V10331076
FDB241 Base adapter, Removing tool for base adapter FDUD290	Installation	A6V10301452
FDB251 Base adapter, Removing tool for base adapter FDUD290	Installation	A6V10411361
FDB281 Base adapter	Installation	008116
FDB299 Base adapter, Removing tool for base adapter FDUD290	Installation	A6V10301448

FD20 Ex-protected devices		
SB2, SB3 Safety Barriers	Data sheet	001222
SB2, SB3 Shunt Zener Diode Barriers	Installation	1227
DT1101A-Ex, DT1102A-Ex. DO1101A-Ex Automatic fire detectors for explosion-hazard areas of zones 1 and 2	Data sheet	001469
DF1101-Ex Infrared flame detector for explosion-hazard areas of zones 1 and 2	Data sheet	001744
FDAI92-Ex, FDAI93-Ex Alarm indicators for explosion-hazard areas for zones 1 and 2	Data sheet	A6V10276518
FDAI92-Ex, FDAI93-Ex, AI330, DCA1191, DJZ1193 Alarm indicators, adapter frame, surface-mounted housing, indicator housing, incl. washer	Installation	A6V10260486
DM1103(Ex), DM1104(Ex) Manual call points collective/SynoLINE600 for explosion-hazard areas of zones 1 and 2	Data sheet	A6V10236643
DO1101A-Ex, DT1101A-Ex, DT1102A-Ex Wide spectrum smoke detector, collective Heat detectors, collective, intrinsically safe	Technical manual	1485
DF1191, DF1192, DF1192 (UL/ULC), DF1101-Ex, DF1101-Ex (UL/ULC), DF1151-Ex Infrared flame detectors	Technical manual	1673
DF11xx(-Ex) Infrared flame detectors (for explosion hazard areas of zone 1 and 2)	Commissioning	1677
DB3 Audible alarm device for ex-hazard areas of zones 1 and 2	Data sheet	009001
FDCL221-Ex Line adapter (Ex)	Data sheet	A6V10349349
FDCL221-Ex Line adapter (Ex)	Technical manual	A6V10333771
FDCL221-Ex Line adapter (Ex)	Installation	A6V10349626
FDOOT241-A9-Ex Automatic fire detector	Data sheet	A6V10349345
FDOOT241-A9-Ex Automatic fire detector	Technical manual	A6V10346580
FDOOT241-A9-Ex Automatic fire detector	Installation	A6V10349621
FDM223-Ex Manual call point	Data sheet	A6V10349347
FDM223-Ex Manual call point	Technical manual	A6V10349616
FDM223-Ex Manual call point	Installation	A6V10349619
Fire detection installations with addressed detector lines in potentially explosive atmospheres	Technical manual	A6V10324618
Modernizing fire detection installations with multiple protocol detectors in areas at risk of explosion	Technical manual	A6V10443621
FD20 Service devices		
Test units and accessories FDUL221, FDUD29x, FDUD29x-E, RE6, REF8, REF8-S, REF8-C, RE8, RE8-S, RE8-C, RE7T, RE8ST, RE8STCO, RE8-CO, RE7T-x, RE10, FDUM29x, FDLU291, LE3, StabexHF	Data sheet	007228
FDUD292 Detector exchanger and tester	Technical manual	007227
FDUD293 Intelligent detector tester	Technical manual	009718
FDUL221 Line tester	Technical manual	008250
FDUZ227 MCL-USB adapter (radio)	Data sheet	A6V10355605
FDUZ227 MCL-USB adapter (radio)	Installation	A6V10347735
LE3 Test Lamp	Operation	000257
DZW1171 Radio Test Set	Operation	004446
RE7T Solo461 Heat detector tester kit	Operating instruction	A6V10254740
RE7T-C, Solo 725 charger for RE7T-B	Operating instruction	A6V10260320
RadioSpy	Technical manual	A6V10229812
RadioSpy	Installation	A6V10217915

FD20 Applications		
FD20 Detector system	Acceptance test fire (Guideline)	009977
Sinteso™ Fire detector	Application guideline	010030
Migration of MS8 Detectors (only available in German)	Application	A6V10224857
FS20 Fire detection System Overview		
FS20 Sinteso Fire detection system	Data sheet	008955
FC2020 Fire Control Panel	Data sheet	009383
FC2030 Fire Control Panel	Data sheet	A6V10087532
FC2040 Fire Control Panel	Data sheet	009384
FC2060 Fire Control Panel	Data sheet	A6V10087844
FC2080 Fire Control Panel	Data sheet	A6V10275515
FT2080 Fire terminal (Touch)	Data sheet	A6V10378271
FG2020-DZ Gateway (SIGMANET) [DE] (only available in German)	Data sheet	A6V10400543
FT2040 Fire Terminal	Data sheet	009386
FT2010 Floor repeater terminal FT2011 Floor repeater display	Data sheet	009393
FT2001-A1 Mimic display driver F50F410 LED flat cable	Data sheet	A6V10082691
FS20 Fire detection system	Components / Spare parts / Repair parts	009690
FCM2008-N1, FCM7221-H3, FTI2002-N1, FT2003-N1, Detached evacuation panel	Data sheet	A6V10223093
FP2015-A1 Power supply (70 W)	Data sheet	A6V10367041
FN2012-A1 Ethernet switch (modular)	Data sheet	A6V10455902
VN2002-A1 / VN2003-A1 Ethernet Module (MM) / (SM)	Data sheet	A6V10455908
FS20 Fire detection description		
FS20 Fire detection system	Description	008836
FG2020 Technical manual	Technical manual	A6V10281424
FS20 Fire detection planning		
FS20 Fire detection system	Planning	008843
FS20 Fire detection characteristics product data		
FS20 Fire detection system	Characteristic product data	008837
FS20 Fire detection mounting/installation		
Fire control panel / Fire terminal Fx20xx	Mounting	009197
Floor repeater terminal FT2010 Floor repeater display FT2011	Mounting	008860
Component Fx20xx	Mounting	009200
FS20 Fire detection system	Installation	008851
FS20 Fire detection system	Inscription strips	009026
FS20 Fire detection system (only available in German)	Quick guide	010108
Mimic display driver FT2001-A1, LED flat cable F50F410	Mounting	A6V10088169
FHA2016-A1, 19" mounting kit	Mounting	A6V10332588
FP2015 - Power Supply Equipment 24V/70W	Mounting	A6V10432440
FP2001-A1 Power supply (70 W) SV 24V-150W-A5 Power supply (150 W)	Mounting	A6V10432442
FN2012-A1 Ethernet-switch (modular)	Mounting	A6V10457371
FN2001-A1 Repeater (SAFEDLINK)	Mounting	A6V10705064
FM blind (1HU) FHA2017-A1 FM blind (2HU) FHA2015-A1	Mounting	A6V10331435
FG2020 Gateway (Sigmanet) (only available in German)	Mounting	A6V10367946
FT2080 Fire terminal (Touch)	Mounting	A6V10462660
FHA2039-A1 Rear cover (FT2080)	Mounting	A6V10618184
FHA2040-A1 Desktop housing (FT2080)	Mounting	A6V10618186
FC2030-CR / FHA2055-A1 Brandmeldezentrale (Unterputz) [CH] –only available in German	Mounting	A6V10487482

FS20 Fire detection service		
FS20 Fire detection system	Commissioning / Maintenance / Troubleshooting	009052
FS20 Fire detection system	Configuration	009078
FXS2015 Sinteso Mobile	Commissioning	A6V10415916
Sinteso Test (for FDUD292 and a Bluetooth extension kit FDUD29x-E)	Technical Manual	A6V10424692
FS20 Fire detection operation		
FC20xx Fire control panel, FT2040 fire terminal	Operation	008838
FC20xx Fire control panel, FT2040 fire terminal	Operation (short)	009906
FT2010 Floor repeater terminal	Operation	009310
FT2011 Floor repeater display	Operation	009311
Operation Sigmasys GW FG2020 (only available in German)	Operation	A6V10327208
FT2080 Fire terminal (Touch)	Operation	A6V10380629
FT2080 Fire terminal (Touch)	Operation (brief)	A6V10380636
FS20 Application Guide		
FS Fire detection system Lightning protection and voltage surge protection	Application Guide	A6V10225306
FS20 Fire detection system, External printer	Application Guide	A6V10224853
FS20 Site conversion	Commissioning	A6V10244961
FX2010 Quantities tool	Quantities tool	009716

Siemens Switzerland Ltd
Building Technologies Division
International Headquarters
Gubelstrasse 22
CH-6301 Zug
Tel. +41 41 724 24 24
www.siemens.com/buildingtechnologies

© Siemens Switzerland Ltd, 2016
Technical specifications and availability subject to change without notice.

Dokument ID A6V10886554_en--_b
Edition 2016-04-29