

# CQD/NGG

## Max-Flex, Flange Mounted, Variable Depth Operator



The Max-Flex™ flange mounted variable depth operator allows for the greatest degree of flexibility for operating the Siemens CQD and NGG compact enclosed molded case circuit breakers.

Due to the great ease of installation, the Siemens Max-Flex operator offers a substantial time and labor savings to the user when compared to other types of flange mounted operators.

The Max-Flex handle when mounted onto the enclosure flange, will accept up to three padlocks with a maximum shackle diameter of 3/8 inch.

# max-flex

# OPERATOR

# SIEMENS

Enclosure Type	Application Length Inches	Complete Kit Catalog Number	Catalog Number Handle Only	Catalog Number Breaker Operator	Catalog Number Cable Only
1, 12, 3R	36	<b>MFKG3R3</b>			<b>MFCF036</b>
	48	<b>MFKG3R4</b>			<b>MFCF048</b>
	60	<b>MFKG3R5</b>			<b>MFCF060</b>
	72	<b>MFKG3R6</b>			<b>MFCF072</b>
	84	<b>MFKG3R7</b>	<b>MFHM3R</b>	<b>MFMG</b>	<b>MFCF084</b>
	96	<b>MFKG3R8</b>			<b>MFCF096</b>
	108	<b>MFKG3R9</b>			<b>MFCF108</b>
	120	<b>MFKG3R10</b>			<b>MFCF120</b>
	144	<b>MFKG3R12</b>			<b>MFCF144</b>

Enclosure Type	Application Length Inches	Complete Kit Catalog Number	Catalog Number Handle Only	Catalog Number Breaker Operator	Catalog Number Cable Only
4X	36	<b>MFKG4X3</b>			<b>MFCF036</b>
	48	<b>MFKG4X4</b>			<b>MFCF048</b>
	60	<b>MFKG4X5</b>			<b>MFCF060</b>
	72	<b>MFKG4X6</b>			<b>MFCF072</b>
	84	<b>MFKG4X7</b>	<b>MFHM4X</b>	<b>MFMG</b>	<b>MFCF084</b>
	96	<b>MFKG4X8</b>			<b>MFCF096</b>
	108	<b>MFKG4X9</b>			<b>MFCF108</b>
	120	<b>MFKG4X10</b>			<b>MFCF120</b>
	144	<b>MFKG4X12</b>			<b>MFCF144</b>