

# Outdoor Combination Metering

CATALOG NUMBER:

## JA0816B1400RLTM

FOR OVERHEAD AND UNDERGROUND SERVICE SURFACE MOUNT

ENCLOSURE  
TYPE 3R

**SUITABLE ONLY FOR USE AS SERVICE EQUIPMENT.**

**CAUTION:** CIRCUIT MAY BE LIVE WITH METER REMOVED.


DEVICE RATING:  
400 AMPS MAXIMUM; 120/240 V ~ (4 JAW) OR 208Y/120 V ~ (5 JAW); SINGLE PHASE, THREE WIRE.

METER SOCKET: 4 JAW; LEVER OPERATED BYPASS WITH JAW TENSION RELEASE.

RATING: 400 AMPS (320 AMPS CONTINUOUS)

HARDWARE TIGHTENING TORQUES:

3/8 NUTS ..... 250-350 IN.-LBS.



TERMINAL RANGES, kcmil OR AWG; CU/AL:	TORQUE, LB.-IN.:
□ (1)600kcmil-#4 OR (2)350kcmil-1/0	500
⊗ (1)250kcmil-6	250
⊕ (1)2/0-#12	50
⊙ (1) 500kcmil-3/0 OR (2) 250kcmil-3/0	450
⊖ (1)250kcmil - 6	275
<b>NEUTRAL BAR TERMINALS</b>	
<b>SMALL</b> (1) #10-#14	20
(1) #8	25
(1) #6	35
<b>LARGE</b> (1) #10-14	35
(1) #8	40
(1) 1/0 - #6	45

ACCESSORIES	
FILLER PLATE	ECQF3
5TH JAW SHIELD	S35815-2
FOR HUB, ORDER FROM "HD" SERIES	
COVERPLATE	EC56933S
3" HUB	EC56856
3 1/2" HUB	EC56857
4" HUB	EC56858