

Outdoor Combination Metering

CATALOG NUMBER:

JC0404L1400RLM

ENCLOSURE
TYPE 3R


FOR OVERHEAD AND UNDERGROUND
SERVICE SURFACE MOUNT

**SUITABLE ONLY FOR USE AS SERVICE
EQUIPMENT.**

CAUTION: CIRCUIT MAY BE LIVE WITH
METER REMOVED.

DEVICE RATING:
400 AMPS MAXIMUM; 120/240 V ~ (4 JAW) OR
208Y/120 V ~ (5 JAW); SINGLE PHASE, THREE
WIRE.

METER SOCKET: 4 JAW; LEVER OPERATED
BYPASS WITH JAW TENSION RELEASE.
RATING: 400 AMPS (320 AMPS CONTINUOUS)



TERMINAL TIGHTENING TORQUES LB.-IN.:

WIRE SIZE	□	⊗	⊕	⊙
600 - 500 kcmil	500	-	-	-
500 - 350 kcmil	500	-	-	450
350kcmil-3/0	500	250	-	450
2/0	-	250	50	-
1/0-#6	-	250	50	-

TERMINAL RANGES, kcmil OR AWG:

□	= LIMITED TO (1)600kcmil-#4 OR (2)350kcmil-1/0
⊗	= (1)#250kcmil-6
⊕	= (1)2/0-#12
⊙	= LIMITED TO (1) 500kcmil-3/0 OR (2) 250kcmil-3/0

ACCESSORIES

FILLER PLATE	QF3
5TH JAW SHIELD	S35815-2
FOR HUB, ORDER FROM "HD" SERIES	
COVERPLATE	S56933
3" HUB	S56856-2
3 1/2" HUB	S56857-2
4" HUB	S56858-2

HARDWARE TIGHTENING TORQUES:
3/8 NUTS 250-350 IN.-LBS.