

# Portable Generators

## 5 kW

### Features

- Ideal for residential emergency and job-site power
- Gasoline powered, 389cc OHV engine
- Includes handles and wheels for easy movement
- Hour meter included
- Large variety of outlets
- Low noise muffler
- Manual recoil starter
- 2 year warranty
- Easily integrated into home electrical system with Siemens breaker interlock kits (pictured below)



ECSBPK01 Breaker Interlock Kit



Running Watts	5000 Watts
Starting Watts	6250 Watts
Engine Size and Type	389cc OHV
Engine Design Life	1,000 + Hours
Pressure Lube w/Filter	No
Starting Method	Recoil
Battery Included	N/A
Covered Outlets	No
Outlets	4x5-20R 1xL14-30R
Hour Meter w/ Maintenance Resets	Yes
Low Oil Shutdown	Low Level
Fuel Tank Type and Size	Steel, 6.6 Gal.
Run Time at 50%	10 Hours
Handles	Fold Down/Locking
First Oil Included	Yes
Emission Certified	49 States <sup>①</sup>
Warranty	2 Year Limited
Dimensions (inches) LxWxH	33.5 x 26.5 x 27.5
Product Weight	180 lbs.

① Certified in all states except California

### Data Sheet

[www.sea.siemens.com/generators](http://www.sea.siemens.com/generators)

**SIEMENS**

Siemens Energy & Automation, Inc.  
3333 Old Milton Parkway  
Alpharetta, GA 30005

1-800-964-4114  
info.sea@siemens.com

©2008 Siemens Energy & Automation, Inc.  
All Rights Reserved. Siemens is a registered  
trademark of Siemens AG. Product names  
mentioned may be trademarks or registered  
trademarks of their respective companies.  
Specifications are subject to change without  
notice.

RPFL-PORTA-0908 (New) 0908POD

[www.sea.siemens.com/generators](http://www.sea.siemens.com/generators)