


200A SIEMENS F
FRAME BREAKER

28

LINE

#14-#2 GROUND TERMINAL
(3) PLACES

26



2-1/2, 2, 1-1/2, 1-1/4 & 1" KO (4) PLACES

3, 2-1/2, 2, 1-1/2, 1-1/4 & 1" KO (6) PLACES

5/16" KO (2) PLACES

1/2" KO (2) PLACES

7 TERMINAL
LEVER BYPASS
WITH CLAMPING
JAW SOCKET

LEVER BYPASS LABEL

#6-350MCM CU-AL
LINE NEUTRAL, LOAD
AND LOAD NEUTRAL

BREAKER
ACCESS DOOR

7/16 KO FOR
BARREL LOCK

6

NOTES:

- 1) UNIT RATING:
200A, 600 VAC, 3 PHASE, 4 WIRE
- 2) ENCLOSURE IS FABRICATED FROM
14GA GALVANIZED STEEL, FRONTS, TOP
& BOTTOM FROM 16GA GALVANIZED STEEL.
- 3) FINISH: GRAY

| | | | | | |
|--|---------------|--|-------------------|-----------------------------|--------------|
| UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES | | -CONFIDENTIAL-PROPERTY OF Siemens Industry, Inc. | | | |
| TOLERANCES: .XX .XXX HOLE DIAMETER ANGULAR UNDIMENSIONED 90° ANGLES | | | | | |
| DWN KP | DATE 6/3/2014 | SIZE B | ISSUE RELEASE NO. | DWG NO. SELG0303CS3200RD | REV |
| CHK | DATE | SCALE | | DO NOT SCALE DRAWING | SHEET 1 OF 1 |
| APVD | DATE | | | | |