


5 X 5 HUB COVER PLATE



#14-1/0 GROUND TERMINAL
(3) PLACES

400A SIEMENS J
FRAME BREAKER

BREAKER
ACCESS COVER

7 TERMINAL LEVER
BYPASS CLAMPING
JAW SOCKET

LEVER BYPASS LABEL


7/16 KO FOR
BARREL LOCK

#4-500MCM OR DUAL
1/0-250MCM CU-AL
LINE NEUTRAL, LOAD
AND LOAD NEUTRAL

13

56

6



5/16" KO

1/2" KO

3, 2-1/2, 2, 1-1/2, 1-1/4 & 1" KO
(6) PLACES

- NOTES:
- 1) UNIT RATING:
320A, 600 VAC, 3 PHASE, 4 WIRE
 - 2) ENCLOSURE IS FABRICATED FROM
16GA GALVANIZED STEEL
 - 3) FINISH: GRAY

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES

TOLERANCES:
.XX
.XXX
HOLE DIAMETER
ANGULAR
UNDIMENSIONED 90° ANGLES

DWN 6/4/2014	DATE	KP	SIZE B	ISSUE RELEASE NO.	DWG NO.	REV
CHK	DATE				SELG0303CS400R	
APVD	DATE		SCALE	DO NOT SCALE DRAWING	SHEET 1 OF 1	

-CONFIDENTIAL-PROPERTY OF
Siemens Industry, Inc.

SKT/BKR 320A 3P HCP