



NOTES:

- 1) FINISH: GRAY
- 2) CABINET: BACK IS FABRICATED FROM 14 GA GALV STEEL. TOP, BOTTOM, BARRIER AND FRONT IS FABRICATED FROM 16 GA GALV STEEL.
- 3) 200 AMP, 120/240 VAC, 3 PHASE, 4 WIRE
- 4) SEALING RING, HUB COVER PLATE ASY, & NEMA INSTR SHEET PLACED INSIDE OF BOX BEFORE DEADFRONT IS SECURED.
- 5) UL LISTED - FILE E27485
- 6) EUSERC DRAWING NUMBER 305A.

LANDIS & GYR CATALOG NO:
MM0303F3200CEY
TYPE 3R ENCLOSURE (RAINPROOF).

FEED:
TOP OR BOTTOM

BREAKER LOCATION:
SIDE SECTION

SUITABLE FOR USE AS SERVICE EQUIPMENT WHEN NOT MORE THAN SIX MAIN DISCONNECTING MEANS ARE PROVIDED. WHEN USED AS SERVICE EQUIPMENT, BOND NEUTRAL AND APPLY "SERVICE DISCONNECT" LABEL NEAR THE DISCONNECT HANDLE.

DEVICE RATING: 200 AMPS MAXIMUM; 208Y/120 OR 240/120 VAC DELTA*, THREE PHASE, FOUR WIRE.

METER SOCKET RATING: 200 AMPS CONTINUOUS.

*CONNECT HIGH PHASE (208V TO GROUND) TO RIGHT HAND TEST BLOCK.

THIS DEVICE HAS A MAXIMUM SHORT CIRCUIT CURRENT RATING OF 100,000 RMS SYMMETRICAL AMPERES AT 240 VAC MAXIMUM. (Watt-Hour meter not included in short circuit current rating), WHEN 300 VOLT CLASS FUSES ARE INSTALLED. REPLACEMENT PULLOUT SWITCH MUST BE OF SAME TYPE, RATING & MANUFACTURER.

TERMINAL TIGHTENING TORQUES, LB-IN.

WIRE SIZE, kcmil or AWG	LINE & NEUTRAL	SERVICE GROUND	EQUIPMENT GROUND	
			LARGE HOLE	SMALL HOLE
250-2/0	250	---	---	---
1/0 - 3	---	50	45	---
4	---	45	45	---
6	---	45	45	35
8	---	40	40	25
10 - 12	---	35	35	20

TORQUE TEST BLOCK CIRCUIT CLOSING (DISCONNECT) NUT (5/8" ACROSS FLATS) TO 50 LB-IN.

PULLOUT SWITCH LOAD: SIZE WIRE IN ACCORDANCE WITH DEVICE RATING AND WIRE BENDING SPACE. SEE MARKINGS ON PULLOUT FOR TORQUE REQUIREMENTS.

TERMINALS SUITABLE FOR USE WITH 60/75°C, AL/CU INSULATED WIRE

FOR EQUIPMENT GROUND BAR ORDER ECLX SERIES, IF HUB IS REQUIRED SELECT FROM "HC" LIST BELOW, OR USE ECHCRXA ADAPTER WITH HUBS SELECTED FROM "RX" LIST BELOW.

HC TYPE HUBS		RX TYPE HUBS	
SIZE	CAT. NO.	SIZE	CAT. NO.
2"EHC200	1-1/2"EC38598
2-1/2"EHC250	2"EC38599
3"EHC300	2-1/2"EC38600

© 2015 Copyright Siemens Industry, Inc.

TALON

RAINPROOF COMBINATION METERING

Description:

SKT 200A 3P HO EUSERC

CJD 11-07-16 DO NOT SCALE DRAWING Dwg No: MM0303F3200CEY