




TEL (915) 590-8500
FAX (915) 590-8510



**Enclosed Switch
General Duty**



Catalog Number **GU221** Enclosure **Type 1** Model **4**

Amperes	Horsepower Rating		
	Volts-PH	Std.	Max.
30	120 AC-1Ø	½	2
	240 AC-1Ø	1-½	3
	240 AC-3Ø	3	7-½

Wire Connector Information:

Line / Neutral Terminals: **USE 14-6 Cu/ 12-6 Al 60°/75° C WIRE**
Load Terminals: **USE 14-8 Cu/ 12-8 Al 60°/75° C WIRE**

WIRE SIZE:	14-10 AWG	8 AWG	6 AWG
NOMINAL TORQUE:	15 LB. IN.	18 LB. IN.	27 LB. IN.

⚠ DANGER	⚠ PELIGRO
 <p>HAZARDOUS VOLTAGE. WILL CAUSE DEATH OR SERIOUS INJURY. Turn off power ahead of switch before doing work inside. Close cover before turning power on.</p>	 <p>VOLTAJE PELIGROSO. CAUSARÁ LA MUERTE O LESIONES GRAVES. Desconectar el suministro de energía al interruptor antes de efectuar cualquier trabajo dentro de la unidad. Cerrar la cubierta antes de conectar la energía.</p>

Fuse & Short Circuit Information:

This switch is suitable for use on a circuit capable of delivering not more than 10,000 amperes, rms symmetrical, **240** Volts Maximum, when protected by fuses or circuit breakers rated 30 Amps maximum. (120 Volts Max. on single pole devices.)

Accessories and Replacement Parts:

Service Equipment:

To bond enclosure to neutral, use No. 10 screw provided.

Equipment Ground Bar Kit: GSGK60M. USE **Cu/Al 60°/75° C WIRE**

WIRE SIZE:	14-10 AWG	8 AWG	6 AWG
NOMINAL TORQUE:	35 LB. IN.	40 LB. IN.	45 LB. IN.

Neutral Assembly: Order Catalog No. W410190M.

This device has been inspected and tested.

Inspection Record No.

Pc. No. 410384H02



Murray Electrical Products
Siemens Industry, Inc.
Norcross, GA 30092 U.S.A.
Assembled in Mexico (E)



.125" RCR

COMPANY NAME	MATERIAL	SIZE	JOB WILL NOT BE PRINTED UNLESS APPROVED BY CUSTOMER.		PART NO.
Siemens Industry, Inc. THIS DOCUMENT IS THE PROPERTY OF LABELTECH, INC. IT'S USE IS AUTHORIZED ONLY FOR RESPONDING TO A REQUEST FOR QUOTATION OR FOR THE PERFORMANCE OF WORK REQUESTED FROM LABELTECH, INC. ALL QUESTIONS MUST BE REFERRED TO THE LABELTECH, INC. PRODUCTION DEPARTMENT.	Semi-Gloss Paper INK COLORS Black	WIDTH	<input type="checkbox"/> OK TO PRINT AS IS	<input type="checkbox"/> MAKE CORRECTIONS, RESUBMIT CORRECTED PROOF	410384H02
		3.75"			
		LENGTH	Label		
		6.00"	REVISION LEVEL		
		CORNER RADIUS	.125"	AUTHORIZED BY	DATE
				CHECKED BY	
				DATE	07/25/11