



TEL (915) 590-8500
FAX (915) 590-8510

3.75"

Enclosed Switch
General Duty

Catalog Number **GUN321** Enclosure Type **1**

Amperes 30	Horsepower Rating			
	Volts-PH	Std.	Max.	DC.
	240-1ø	1-1/2	3	
	240-3ø	3	7-1/2	
	250 DC	-	-	5

Wire Connector Information: **USE 14-6 Cu/ 12-6 Al 60°/75° C WIRE**
Line/Neutral Terminals:
Load Terminals: **USE 14-8 Cu/ 12-8 Al 60°/75° C WIRE**

WIRE SIZE:	14-10 AWG	8 AWG	6 AWG
NOMINAL TORQUE:	15 LB.IN.	18 LB.IN.	27 LB.IN.

⚠ DANGER

HAZARDOUS VOLTAGE. WILL CAUSE DEATH OR SERIOUS INJURY.

Turn off power ahead of switch before doing work inside. Close cover before turning power on.

⚠ PELIGRO

VOLTAJE PELIGROSO. CAUSARA LA MUERTE O LESIONES GRAVES.

Desconectar el suministro de energia al interruptor antes de efectuar cualquier trabajo dentro de la unidad. Cerrar la cubierta antes de conectar la energia.

Fuse & Short Circuit Information:
Suitable for use on circuits capable of delivering not more than 100,000 amperes, rms symmetrical, 240 volts maximum when protected by Class R fuses rated 30 amperes maximum.
DANGER - Unless Class R fuses are used, this switch may present a risk of fire and personal injury if installed on circuits capable of delivering more than 10,000 amperes, rms symmetrical.
PELIGRO - A menos que se usen fusibles clase R, este interruptor representa riesgos de incendio y lesiones personales si se instala en circuitos capaces de entregar más de 10,000 Amperios efectivos simétricos.

When used as a 2 pole switch, use the 2 outside poles.

Accessories and Replacement Parts:
Service Equipment:
To bond enclosure to neutral, use No. 10 screw provided.
Equipment Ground Bar Kit: GSGK60M. USE **CU/AL 60°/75° C WIRE**

WIRE SIZE:	14-10 AWG	8 AWG	6 AWG
NOMINAL TORQUE:	35 LB.IN.	40 LB.IN.	45 LB.IN.

Replacement Base Assembly: Order Catalog No. W410473B.
Neutral Assembly: Order Catalog No. W410190M.

This device has been inspected and tested.
Inspection Record No.

Pc. No. 410387K02

LISTED
ENCLOSED SWITCH
Issue No. AL-265
File No. E4776

Murray Electrical Products
Siemens Industry, Inc.
Norcross, GA 30092
Assembled in Mexico ©

.125" RCR

6.00"

.25"

COMPANY NAME	MATERIAL	SIZE	JOB WILL NOT BE PRINTED UNLESS APPROVED BY CUSTOMER.		PART NO.
Siemens Industry, MTR	UL LITHO	WIDTH 3.75"	<input type="checkbox"/> OK TO PRINT AS IS	<input type="checkbox"/> MAKE CORRECTIONS, RESUBMIT CORRECTED PROOF	410387K02
THIS DOCUMENT IS THE PROPERTY OF LABELTECH, INC. IT'S USE IS AUTHORIZED ONLY FOR RESPONDING TO A REQUEST FOR QUOTATION OR FOR THE PERFORMANCE OF WORK REQUESTED FROM LABELTECH, INC. ALL QUESTIONS MUST BE REFERRED TO THE LABELTECH, INC. PRODUCTION DEPARTMENT.	Lamination: No	LENGTH 6.00"	<input type="checkbox"/> OK TO PRINT WITH CORRECTIONS AS MARKED		DESCRIPTION: Label
	INK COLORS	CORNER RADIUS .125"	AUTHORIZED BY	DATE	REVISION LEVEL H
	Black				DESIGNER Joel Ortega
					CHECKED BY DATE 04/05/12