



TEL (915) 590-8500  
FAX (915) 590-8510

3.75"

6.00"

# SIEMENS

Enclosed Switch Plug Fuse Type  
General Duty

Catalog Number Enclosure  
**LF111N** **Type 1**

Amperes <b>30</b>	Horsepower Rating		
	Volts-PH	Std.	Max.
	120 AC-1Ø	½	2

The starting current of motors more than the standard horsepower rating may require the use of fuses with appropriate time delay characteristics. Continuous load current not to exceed 80 percent of the rating of fuses employed in other than motor circuits.

**Wire Connector Information:**

Line / Neutral Terminals: **USE 14-6 Cu/ 12-6 Al 60°/75° C WIRE**  
Load Terminals: **USE 14-8 Cu/ 12-8 Al 60°/75° C WIRE**

WIRE SIZE:	14-10 AWG	8 AWG	6 AWG
NOMINAL TORQUE:	15 LB. IN.	18 LB. IN.	27 LB. IN.

**⚠ DANGER**

**HAZARDOUS VOLTAGE.**  
**WILL CAUSE DEATH OR SERIOUS INJURY.**

Turn off switch before removing or installing fuses. Turn off power ahead of switch before doing work inside. Close cover before turning power on.

**Fuse & Short Circuit Information:**

This switch is suitable for use on a circuit capable of delivering not more than 10,000 amperes, rms symmetrical, 240 Volts Maximum. (120 Volts Max. on single pole devices.)

**Accessories and Replacement Parts:**

**Service Equipment:**

To bond enclosure to neutral, use No. 10 screw provided.

**Equipment Ground Bar Kit:** GSGK60. USE **Cu/Al 60°/75° C WIRE**

WIRE SIZE:	14-10 AWG	8 AWG	6 AWG
NOMINAL TORQUE:	35 LB. IN.	40 LB. IN.	45 LB. IN.

This device has been inspected and tested.

Inspection Record No.

Pc. No. 410384A02



**Siemens Industry, Inc.**  
Norcross, GA 30092 U.S.A.  
Assembled in Mexico (E)

.125" RCR

COMPANY NAME		MATERIAL		SIZE		JOB WILL NOT BE PRINTED UNLESS APPROVED BY CUSTOMER.		PART NO.	
Siemens Industry, Inc.		Semi-Gloss Paper		WIDTH 3.75"		<input type="checkbox"/> OK TO PRINT AS IS <input type="checkbox"/> MAKE CORRECTIONS, RESUBMIT CORRECTED PROOF		<b>410384A02</b>	
THIS DOCUMENT IS THE PROPERTY OF LABELTECH, INC. IT'S USE IS AUTHORIZED ONLY FOR RESPONDING TO A REQUEST FOR QUOTATION OR FOR THE PERFORMANCE OF WORK REQUESTED FROM LABELTECH, INC. ALL QUESTIONS MUST BE REFERRED TO THE LABELTECH, INC. PRODUCTION DEPARTMENT.		INK COLORS		LENGTH 6.00"		<input type="checkbox"/> OK TO PRINT WITH CORRECTIONS AS MARKED		DESCRIPTION: <b>Label</b>	
		Black		CORNER RADIUS .125"		AUTHORIZED BY		REVISION LEVEL <b>G</b>	
						DATE		DESIGNER <b>Joel Ortega</b>	
								CHECKED BY	
								DATE <b>03/26/10</b>	