



TEL (915) 590-8500
FAX (915) 590-8510

3.75"

6.00"

SIEMENS

Enclosed Switch General Duty Plug Fuse Type

Catalog Number **LF211N** Enclosure **Type 1**

Amperes	Horsepower Rating		
	Volts-PH	Std.	Max.
30	120 AC-1Ø	½	2
	240 AC-1Ø	1-½	3

The starting current of motors more than the standard horsepower rating may require the use of fuses with appropriate time delay characteristics. Continuous load current not to exceed 80 percent of the rating of fuses employed in other than motor circuits.

Wire Connector Information:
Line / Neutral Terminals: **USE 14-6 Cu/ 12-6 Al 60° /75° C WIRE**
Load Terminals: **USE 14-8 Cu/ 12-8 Al 60° /75° C WIRE**

WIRE SIZE:	14-10 AWG	8 AWG	6 AWG
NOMINAL TORQUE:	15 LB. IN.	18 LB. IN.	27 LB. IN.

⚠ DANGER	HAZARDOUS VOLTAGE. WILL CAUSE DEATH OR SERIOUS INJURY. <small>Turn off switch before removing or installing fuses. Turn off power ahead of switch before doing work inside. Close cover before turning power on.</small>	⚠ PELIGRO	VOLTAJE PELIGROSO. CAUSARÁ LA MUERTE O LESIONES GRAVES. <small>Apagar el interruptor antes de remover o instalar el fusible. Desconectar el suministro de energía al interruptor antes de efectuar cualquier trabajo dentro de la unidad. Cerrar la cubierta antes de conectar la energía.</small>
-----------------	--	------------------	--

Fuse & Short Circuit Information:
This switch is suitable for use on a circuit capable of delivering not more than 10,000 amperes, rms symmetrical, 240 Volts Maximum. (120 Volts Max. on single pole devices.)

Accessories and Replacement Parts:
Service Equipment:
To bond enclosure to neutral, use No. 10 screw provided.
Equipment Ground Bar Kit: GSGK60. USE Cu/Al 60°/75° C WIRE
WIRE SIZE: 14-10 AWG 8 AWG 6 AWG
NOMINAL TORQUE: 35 LB. IN. 40 LB. IN. 45 LB. IN.

This device has been inspected and tested.
Inspection Record No. _____
Pc. No. 410384D02



Siemens Industry, Inc.
Norcross, GA 30092 U.S.A.
Assembled in Mexico (E)

.125" RCR

COMPANY NAME		MATERIAL		SIZE		JOB WILL NOT BE PRINTED UNLESS APPROVED BY CUSTOMER.		PART NO.	
Siemens Industry, Inc.		Semi-Gloss Paper		WIDTH 3.75"		<input type="checkbox"/> OK TO PRINT AS IS <input type="checkbox"/> MAKE CORRECTIONS, RESUBMIT CORRECTED PROOF		410384D02	
THIS DOCUMENT IS THE PROPERTY OF LABELTECH, INC. IT'S USE IS AUTHORIZED ONLY FOR RESPONDING TO A REQUEST FOR QUOTATION OR FOR THE PERFORMANCE OF WORK REQUESTED FROM LABELTECH, INC. ALL QUESTIONS MUST BE REFERRED TO THE LABELTECH, INC. PRODUCTION DEPARTMENT.		INK COLORS		LENGTH 6.00"		<input type="checkbox"/> OK TO PRINT WITH CORRECTIONS AS MARKED		DESCRIPTION: Label	
		Black		CORNER RADIUS .125"		AUTHORIZED BY		REVISION LEVEL G	
						DATE		DESIGNER: Joel Ortega	
								CHECKED BY: _____	
								DATE: 03/26/10	