



TEL (915) 590-8500
FAX (915) 590-8510

SIEMENS

Enclosed Switch Plug Fuse Type
General Duty

Catalog Number Enclosure
LF211NR **Type 3R**

Amperes	Horsepower Rating		
30	Volts-PH	Std.	Max.
	120 AC-1Ø	½	2
	240 AC-1Ø	1-½	3

The starting current of motors more than the standard horsepower rating may require the use of fuses with appropriate time delay characteristics. Continuous load current not to exceed 80 percent of the rating of fuses employed in other than motor circuits.

Wire Connector Information:

Line / Neutral Terminals: USE 14-6 Cu/ 12-6 Al 60°/75° C WIRE

Load Terminals: USE 14-8 Cu/ 12-8 Al 60°/75° C WIRE

WIRE SIZE:	14-10 AWG	8 AWG	6 AWG
NOMINAL TORQUE:	15 LB.IN.	18 LB.IN.	27 LB.IN.

Fuse & Short Circuit Information:

This switch is suitable for use on a circuit capable of delivering not more than 10,000 amperes, rms symmetrical, 240 Volts Maximum. (120 Volts Max. on single pole devices.)

Accessories and Replacement Parts:

Service Equipment:
To bond enclosure to neutral, use No. 10 screw provided. Force the screw through the aluminum seal.

Hub Information: Catalog Number: HA075S HA100S HA125S
¾" 1" 1-¼"

Use closure plate screws provided, to mount hubs.

Equipment Ground Bar Kit: GSGK60. USE Cu/Al 60°/75° C WIRE

WIRE SIZE:	14-10 AWG	8 AWG	6 AWG
NOMINAL TORQUE:	35 LB.IN.	40 LB.IN.	45 LB.IN.

⚠ DANGER

HAZARDOUS VOLTAGE, WILL CAUSE DEATH OR SERIOUS INJURY.

Turn off switch before removing, or installing fuses. Turn off power ahead of switch before doing work inside. Close cover before turning power on.

⚠ PELIGRO

VOLTAJE PELIGROSO, CAUSARÁ LA MUERTE O LESIONES GRAVES.

Apagar el interruptor antes de remover o instalar el fusible. Desconectar el suministro de energía al interruptor antes de efectuar cualquier trabajo dentro de la unidad. Cerrar la cubierta antes de conectar la energía.

This device has been inspected and tested.
Inspection Record No. _____

UL LISTED
ENCLOSED SWITCH
Issue No. AL-265
File No. E4776

Siemens Industry, Inc.
Norcross, GA 30092 U.S.A.
Assembled in Mexico (E)

Pc. No. 410384F02

6.00"

3.75"

.125" RCR

COMPANY NAME	MATERIAL	SIZE	JOB WILL NOT BE PRINTED UNLESS APPROVED BY CUSTOMER.		PART NO.	
Siemens Industry, Inc.	Semi-Gloss Paper	WIDTH	<input type="checkbox"/> OK TO PRINT AS IS	<input type="checkbox"/> MAKE CORRECTIONS, RESUBMIT CORRECTED PROOF	410384F02	
THIS DOCUMENT IS THE PROPERTY OF LABELTECH, INC. IT'S USE IS AUTHORIZED ONLY FOR RESPONDING TO A REQUEST FOR QUOTATION OR FOR THE PERFORMANCE OF WORK REQUESTED FROM LABELTECH, INC. ALL QUESTIONS MUST BE REFERRED TO THE LABELTECH, INC. PRODUCTION DEPARTMENT.	LAMINATION: NO	3.75"			<input type="checkbox"/> OK TO PRINT WITH CORRECTIONS AS MARKED	DESCRIPTION:
	INK COLORS	LENGTH	Label			
	Black	6.00"	REVISION LEVEL	G		
		CORNER RADIUS	.125"	AUTHORIZED BY	DATE	DESIGNER
					Gibrán Camacho	
					CHECKED BY	
					DATE	
					04/06/10	