

Catalog Number: MM0404B12010RL


Features and Ratings

- Ringless Type Meter Socket
- 300A Max.
- Outdoor Enclosure (NEMA Type 3R)
- Painted G90 Steel
- 120/240V AC, 1 Phase, 3 Wire
- 208Y/120V AC, 1 Phase, 3 Wire (WITH 5TH JAW INSTALLED)
- 4 Jaw Lever Operated Bypass Meter Socket With Jaw Tension Release
- For Overhead or Underground Service
- HD Type Hub Opening, Cover Plate Installed

Breakers

SERVICE DISCONNECT 1	SERVICE DISCONNECT 2
QNRH	QPH

THIS DEVICE HAS BEEN DESIGNED FOR USE ONLY WITH THOSE CIRCUIT BREAKERS LISTED ABOVE. THE USE OF OTHER CIRCUIT BREAKERS COULD RESULT IN PROPERTY DAMAGE OR PERSONAL INJURY AND WILL VOID THE WARRANTY.



Connectors, Wire Sizes and Torques

CONNECTOR	WIRE SIZE CU/AL	TORQUE
□	(1) 600KCMIL-#4, (2) 350KCMIL-1/0	500 LB.-IN.
□	Alt. Lugs H66732-2 (2) 350KCMIL-#4	275 LB.-IN.
⊞	(1) 2/0 - #12	50 IN.-LBS.
⊞	(1) 250kcmil-4 2/0-#6	250 IN.-LBS.

HARDWARE TIGHTENING TORQUES
3/8" NUTS 250-300 LB.IN.


Accessories

CONDUIT HUBS (HD Type)	
TRADE SIZE	CATALOG No.
3 INCH	EC56856
3-1/2 INCH	EC56857
4 INCH	EC56858

Hub Cover Plate Kit
Cat No: EC56933S

5th Jaw Shield Kit
Cat No: H35815-2

FILLER PLATE KIT
Cat No: ECQF3



© 2016 Copyright Siemens Industry, Inc.

SIEMENS Siemens Industry, Inc.	
METER MAIN	
Description: 300A, 4 JAW, 102/240V AC	
QJ 7/08/2016	DO NOT SCALE DRAWING
Dwg No:	MM0404B12010RL