







**Catalog Number: 47644-82**

**Features and Ratings**

- Ringless Type Meter Socket
- 320A Continuous, 400A Max., 600V AC
- Outdoor Enclosure (NEMA Type 3R)
- Painted G90 Steel Enclosure
- 1 Phase, 3Wire, Commercial Socket
- 4 Jaw Meter Socket
- Meter Socket Type HQ-4SUT
- For Overhead & Underground Service
- 3" Type HD Hub Installed
- Lever Bypass



**Accessories**

| CONDUIT HUBS (HD Type) |                     |
|------------------------|---------------------|
| TRADE SIZE             | CATALOG No.         |
| 3 INCH                 | EC56856 or H56856-2 |
| 3-1/2 INCH             | EC56857 or H56857-2 |
| 4 INCH                 | EC56858 or H56858-2 |
| Hub Cover Plate        | EC56933 or H56933S  |

Meter Opening Cover Plate  
Cat No: H659-0162  
5th Jaw Kit  
Cat. No: EC35815-2

**Connectors, Wire Sizes and Torques**

| CONNECTOR         | PART No. | WIRE SIZE           | HEX DRIVE | TORQUE      |
|-------------------|----------|---------------------|-----------|-------------|
| LINE,LOAD,NEUTRAL | 61300    | (2) 1/0 - 250 kcmil | 1/2"      | 500 IN-LBS. |
| GROUND            | 67554A   | #14 - 2/0 AWG       | ..        | 50 IN-LBS.  |

© 2016 Copyright Siemens Industry, Inc.

**TALON**

**Meter Socket**

Description: **320A Cont, 4 Jaw, HQ-4SUT, 600V AC, Painted Steel Enclosure**

JEL 3/18/16 DO NOT SCALE DRAWING Dwg No: **47644-82**