




**Catalog Number: 9817-9405**

**Features and Ratings**

- Ringless Type Meter Socket
- 400A Continuous, 400A Max., 600V AC
- Outdoor Enclosure (NEMA Type 3R)
- Painted G90 Steel Enclosure
- 2 or 3 Phase, Commercial/Industrial Socket
- Meter Socket Type K-5T
- For Overhead & Underground Service
- Two Large Hub Openings, Cover Plates Installed



(2) TYPE HD (LARGE) HUB OPENINGS  
COVER PLATES INSTALLED



**Accessories**



CONDUIT HUBS (HD Type)		CAT No.	DESCRIPTION
TRADE SIZE	CATALOG No.		
3 INCH	EC56856 or H56856-2	H69623	Bypass
3-1/2 INCH	EC56857 or H56857-2	H69685-1	Isolated Neutral Kit
4 INCH	EC56858 or H56858-2	H69546-1	Hex Magnet Socket Kit
		H69232-1	Insulated T-Handle Kit
		H65050	K-base Insulator Kit
		H63864	K-base Ground Kit
Hub Cover Plate	EC56933 or H56933S		

**Connectors, Wire Sizes and Torques**

CONNECTOR	PART No.	HEX DRIVE	WIRE SIZE	TORQUE
LINE/LOAD	58853	5/16"	(2)#6 - 350 kcmil	275 IN-LBS.
LINE/LOAD/NEUT	56732*	5/16"	(2)#6 - 350 kcmil	275 IN-LBS.
LINE/LOAD/NEUT	56732-M	3/8"	(2)#4 - 500 kcmil	375 IN-LBS.
GROUND	56734	5/16"	#6 - 250 kcmil	275 IN-LBS.

\*Factory Installed

VIEW SHOWN WITH COVER REMOVED



© 2015 Copyright Siemens Industry, Inc.

**TALON**

**Meter Socket**

Description: **400A Cont, 4 Terminal, K-5T, 600V AC, Painted Steel Enclosure**

JEL 12/1/15 DO NOT SCALE DRAWING Dwg No: **9817-9405**