




**Catalog Number: 9817-9527**

**Features and Ratings**

- Ringless Type Meter Socket
- 480A Continuous, 600A Max., 600V AC
- Outdoor Enclosure (Type 3R)
- Aluminum Enclosure
- 3 Phase, Commercial/Industrial Socket
- Meter Socket Type K-7T
- For Overhead & Underground Service
- Two Large Hub Openings, HD Type Cover Plates Installed



(2) TYPE HD (LARGE) HUB OPENINGS COVER PLATES INSTALLED



**Accessories**

CONDUIT HUBS (HD Type)	
TRADE SIZE	CATALOG No.
3 INCH	EC56856 or H56856-5
3-1/2 INCH	EC56857 or H56857-5
4 INCH	EC56858 or H56858-5
Hub Cover Plate	EC56933 or H56933-1




CAT No.	DESCRIPTION
H69623	Bypass
H69685-1	Isolated Neutral Kit
H69546-1	Hex Magnet Socket Kit
H69232-1	Insulated T-Handle Kit
H65050	K-base Insulator Kit
H63864	K-base Ground Kit

**Connectors, Wire Sizes and Torques**

CONNECTOR	PART No.	HEX DRIVE	WIRE SIZE	TORQUE
LINE	56427-M	3/8"	(2)#2 - 500 kcmil	375 IN-LBS.
LOAD	56732-M	3/8"	(2)#4 - 500 kcmil	375 IN-LBS.
NEUTRAL	56732-M	3/8"	(2)#4 - 500 kcmil	375 IN-LBS.
LINE/LOAD/NEUT	68752-1	5/16"	(3)#6 - 250 kcmil	275 IN-LBS.
GROUND*	56734	5/16"	#6 - 250 kcmil	275 IN-LBS.

\*Factory Installed

VIEW SHOWN WITH COVER REMOVED



© 2019 Copyright Siemens Industry, Inc.

**TALON**  
**Meter Socket**

Description: **480A Cont, 4 Terminal, K-7T, 600V AC, Aluminum Enclosure**

JEL 9/4/19 DO NOT SCALE DRAWING Dwg No: **9817-9527**