


Catalog Number: UAB417-150

Features and Ratings







- Ringless Meter Cover
- 1 Phase, 3 Wire, 240 VAC
- Painted G90 Steel
- 200A Breaker Factory Installed
- Meter Socket Rating: 200A Continuous
- 4 Jaw Meter Socket, Ringless Type Meter Cover
- 10,000 AIC Max. Rated (See Wiring Diagram for Details)
- For Overhead or Underground Service
- RX Type Hubs on Top End Wall



TYPE RX (SMALL) HUB PROVISION
COVERPLATE INSTALLED (NOT SHOWN)

Accessories

TYPE RX HUBS	
Trade size (in)	Catalog number
1 1/4"	EC38597 or H38597-2
1 1/2"	EC38598 or H38598-2
2"	EC38599 or H38599-2
2 1/2"	EC38600 or H38600-2
Closure plate	EC38595 or H38595-1



Siemens Industry, Inc.		
Meter/Breaker Combination		
Description:		
200A, OH/UG, Ringless, Painted G90 Steel		
NH 10/12/15	DO NOT SCALE DRAWING	Dwg. No. UAB417-150