


Molded Case Circuit Breakers

LMD-Frame Sentron™ Series Circuit Breaker

2 & 3-Pole; 500-800 Amperes



Ratings & Markings (UL 489 AIR Interrupting Ratings)

Breaker Type	RMS Symmetrical Amperes (kA)							
	Volts AC (50/60Hz)			Volts DC		Frame Only - Interchangeable Trip		
	240	480	600	250	500	Breaker Type	Frame (2-Pole)	Frame (3-Pole)
LMD6, LMXD6	65	50	25	30 (2-P)	25 (3-P)	LMD6	LMD62F800	LMD63F800
HLM6, HLMXD6	100	65	50	30 (2-P)	50 (3-P)	HLM6	HLM62F800	HLM63F800

Dimensions

Breaker Type	Length	Width	Depth	D-1 (to handle)
LMD6, LMXD6, HLM6, HLMXD6, LMXD6-ETI	16 in.	7.5 in.	4.5 in.	5.93 in.

Frames

Trip Amperage	Poles	Breaker-Type Non-interchangeable Trip		Breaker-Type Interchangeable Trip		Trip Unit Only
		LMXD6	HLMXD6	LMD6	HLM6	
500	2	—	—	LMD62B500	HLM62B500	LMD62T500
600	2	LMXD62B600	—	LMD62B600	HLM62B600	LMD62T600
700	2	LMXD62B700	—	LMD62B700	HLM62B700	LMD62T700
800	2	LMXD62B800	—	LMD62B800	HLM62B800	LMD62T800
500	3	LMXD63B500	HLMXD63B500	LMD63B500	HLM63B500	LMD63T500
600	3	LMXD63B600	HLMXD63B600	LMD63B600	HLM63B600	LMD63T600
700	3	LMXD63B700	HLMXD63B700	LMD63B700	HLM63B700	LMD63T700
800	3	LMXD63B800	HLMXD63B800	LMD63B800	HLM63B800	LMD63T800

Frames - Magnetic Trip Only - ETI Motor Circuit Protector

Ampere Rating	Poles	Minimum	Maximum	LMXD6
800	3	2800	6000	LMXD63L800
800	3	3200	8000	LMXD63A800

Frames - Molded Case Switch - Circuit Disconnect

Ampere Rating	Poles	LMXD6
800	3	LMXD63S800A

Lugs For 75°C Wire

Catalog Number	Cables Per Lug	Wire Range
TA2K500	1, 2	#1-500 kcmil Cu / Al
TA3K500	1-3	#1/0-500 kcmil Cu / Al
TA2N750	1, 2	500-750 kcmil Cu / Al

Shunt Trip Combinations

Control Voltage		1 Shunt Trip	1 Shunt Trip and 1 Auxiliary Switch
AC	DC	Catalog Number	Catalog Number
24	—	S17JLD6	—
48	—	S18JLD6	—
120	—	S01JLD6	S01JLD62A
240	—	S03JLD6	S03JLD62A
277	—	S15JLD6	S15JLD64A
480	—	S04JLD6	—
—	12	S16JLD6	S16JLD62A
—	24	S07JLD6	S07JLD62A
—	48	S09JLD6	S09JLD62A
—	125	S11JLD6	S11JLD62A
—	250	S13JLD6	S13JLD62A

Auxiliary Switch Combinations

Maximum Voltage		1 Form C	2 Form C
AC	DC	Catalog Number	Catalog Number
480	250	A01JLD64	A02JLD64
—	12	A01JLDLV	A02JLDLV

Alarm Switch Combinations

Maximum Voltage		1 Alarm Switch	1 Alarm Switch and 1 Auxiliary Switch	1 Alarm Switch and 2 Auxiliary Switches
AC	DC	Catalog Number	Catalog Number	Catalog Number
480	250	B01JLD64	A01JLD64B	A02JLD64B

Undervoltage Trip Combinations

Control Voltage		1 Undervoltage Trip	1 Undervoltage Trip and 1 Auxiliary Switch	1 Undervoltage Trip and 2 Auxiliary Switches
AC	DC	Catalog Number	Catalog Number	Catalog Number
120	—	U01JLD6	U01JLD62A	U01JLD62AA
208	—	U02JLD6	U02JLD62A	U02JLD62AA
240	—	U03JLD6	U03JLD62A	U03JLD62AA
480	—	U06JLD6	U06JLD64A	U06JLD64AA
—	24	U13JLD6	U13JLD62A	U13JLD62AA
—	48	U14JLD6	U14JLD62A	U14JLD62AA
—	125	U10JLD6	U10JLD62A	U10JLD62AA
—	250	U12JLD6	U12JLD62A	U12JLD62AA

Siemens Industry, Inc.
5400 Triangle Parkway
Norcross, GA 30092

1-800-241-4453
info.us@siemens.com

Subject to change without prior notice
Order No. CBDS-LMDGN-0717
Printed in USA
All Rights Reserved
© 2017, Siemens Industry, Inc.
usa.siemens.com/circuitbreakers

The technical data presented in this document is based on an actual case or on as-designed parameters, and therefore should not be relied upon for any specific application and does not constitute a performance guarantee for any projects. Actual results are dependent on variable conditions. Accordingly, Siemens does not make representations, warranties, or assurances as to the accuracy, currency or completeness of the content contained herein. If requested, we will provide specific technical data or specifications with respect to any customer's particular applications. Our company is constantly involved in engineering and development. For that reason, we reserve the right to modify, at any time, the technology and product specifications contained herein.