




Catalog Number: 9810-8530

Features and Ratings




- Ringless Type Meter Socket
- 400A CU / 395 AL Continuous, 300V AC
- Outdoor Enclosure (NEMA Type 3R)
- Painted G90 Steel Enclosure
- 1 Phase, 3-Wire
- Meter Socket Type K-4UT
- For Overhead & Underground Service
- HD Type Hub Opening, Cover Plate Installed



TYPE HD (LARGE) HUB OPENING
COVER PLATE INSTALLED



VIEW SHOWN WITH COVERS REMOVED



Accessories

| CONDUIT HUBS (HD Type) | |
|------------------------|---------------------|
| TRADE SIZE | CATALOG No. |
| 3 INCH | EC56856 or H56856-2 |
| 3-1/2 INCH | EC56857 or H56857-2 |
| 4 INCH | EC56858 or H56858-2 |
| Hub Cover Plate | EC56933 or H56933S |

K4 Lexan Shield Cat No: 5007400-K
K4 Manual Bypass Cat No: H56495

Blank Sliding Cover
Steel - Cat. No: HA-300529-3
Aluminum - Cat. No: HA-300529-4

Connectors, Wire Sizes and Torques

| CONNECTOR | PART No. | WIRE SIZE | TORQUE |
|-----------|----------|--------------------|-------------|
| LINE | 56427 | (2) #6 - 350 kcmil | 275 IN-LBS. |
| LOAD | 56425 | (2) #6 - 350 kcmil | 275 IN-LBS. |
| NEUTRAL | 56426 | (4) #6 - 350 kcmil | 275 IN-LBS. |
| GROUND | 56734 | #6 - 250 kcmil | 275 IN-LBS. |

© 2019 Copyright Siemens Industry, Inc.

TALON

Meter Socket

Description: **400A Cont, 4 Terminal, K-4UT, 300V AC, Painted Steel Enclosure**

KAM 1/4/19 DO NOT SCALE DRAWING Dwg No: **9810-8530**