


# Catalog Number: 47705-81

## Features and Ratings

- Ringless Type Meter Socket
- 320A Continuous, 400A Max., 600V AC
- Outdoor Enclosure (Type 3R)
- Painted G90 Steel Enclosure
- 1 or 3 Phase, 3 Wire, Commercial Socket
- 5 Jaw Meter Socket, 5th Jaw at 6 o'Clock Position
- Meter Socket Type HQ-5D
- For Overhead & Underground Service
- HD Type Hub Opening
- Lever Bypass



### Accessories






CONDUIT HUBS (HD Type)	
TRADE SIZE	CATALOG No.
3 INCH	EC56856 or H56856-2
3-1/2 INCH	EC56857 or H56857-2
4 INCH	EC56858 or H56858-2
Hub Cover Plate	EC56933 or H56933S

Meter Opening Cover Plate  
Cat No: H659-0162

### Connectors, Wire Sizes and Torques

CONNECTOR	PART No.	WIRE SIZE	TORQUE
LINE/LOAD	60162	(1) #4-600 kcmil (2) 1/0-250 kcmil	500 IN-LBS.
NEUTRAL	61300	(1) #4-600 kcmil (2) 1/0-250 kcmil	500 IN-LBS.
GROUND	67554	#14 - 2/0 AWG	50 IN-LBS.

Wire bending space for up to (2)250 kcmil or up to (1)300 kcmil.



© 2019 Copyright Siemens Industry, Inc.



Description: <b>320A Cont, 5 Jaw, HQ-5D, 600V AC, Painted Steel Enclosure</b>			
KAM 4/8/19	DO NOT SCALE DRAWING	Dwg No:	<b>47705-81</b>