



NOTES:

- 1) FINISH: GRAY
- 2) CABINET: 16GA CRS
- 3) 100 AMP CONTINUOUS PER POSITION  
300 VAC, 1 PHASE, 3 WIRE  
240 AMP (TOTAL) UNIT RATING COPPER  
200 AMP (TOTAL) UNIT RATING ALUMINIUM
- 4) CAT# LABEL ON FRONT COVERS IN LOWER L/H CORNER.
- 5) INSTALLATION INSTRUCTION SHEET INCLUDED

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES  
 TOLERANCES:  
 .XX  
 .XXX  
 HOLE DIAMETER  
 ANGULAR  
 UNDIMENSIONED 90° ANGLES

DWN	JO	DATE	2-11-97
CHK		DATE	
APVD		DATE	

1-3-07	REV UL LBL CJD	TC
4-10-01	ADD TUBE INSUL TO 5-TERM BUS	TC
3-20-97	ADDED INSTRUC SHEET	TC

PRODUCT RATING LABEL

UL LISTING MARK

-CONFIDENTIAL-PROPERTY OF  
**Siemens Energy & Automation, Inc.**  
 Residential Products Division

MTR SKT 2 POS 100A 5T VERT

SIZE	ISSUE RELEASE NO.	DWG NO.	REV
B		UVS210	
SCALE	DO NOT SCALE DRAWING	SHEET	1 OF 1