



UL LISTING MARK

- NOTES:
- 1) FINISH: GRAY
 - 2) CABINET: 16GA CRS
 - 3) 100 AMP CONTINUOUS PER POSITION
300 VAC, 1 PHASE, 3 WIRE
240 AMP (TOTAL) UNIT RATING COPPER
200 AMP (TOTAL) UNIT RATING ALUMINIUM
 - 4) CAT# LABEL ON FRONT COVER IN LOWER L/H CORNER.
 - 5) INSTALLATION INSTRUCTION SHEET INCLUDED

PRODUCT RATING LABEL

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES

TOLERANCES:
.XX
.XXX

HOLE DIAMETER
ANGULAR
UNDIMENSIONED 90° ANGLES

1-05-07	REV PER 2006-177 CJD	DWN	JO	DATE	2-12-97
03/27/03	ADDED X4392 SAFETY GUIDE (4) JMS	CHK		DATE	
4-6-01	ADD TUBE INSUL TO 5-TERM BUS TC	APVD		DATE	
4-25-97	REV TO APPROVAL DWG JO				
3-20-97	ADDED INSTRUC SHEET TC				

DATE 2-12-97

DATE

DATE

-CONFIDENTIAL-PROPERTY OF
Siemens Energy & Automation, Inc.
Residential Products Division

MTR SKT 3 POS 100A 5T VERT 1 BLANK

SIZE	ISSUE RELEASE NO.	DWG NO.	REV
B		UVS311B	
SCALE	DO NOT SCALE DRAWING	SHEET	1 OF 1