



NOTES:

- 1) FINISH: GRAY
- 2) CABINET: 166A CRS
- 3) 100 AMP CONTINUOUS PER POSITION  
300 VAC, 1 PHASE, 3 WIRE  
240 AMP (TOTAL) UNIT RATING COPPER  
200 AMP (TOTAL) UNIT RATING ALUMINIUM
- 4) CAT# LABEL ON FRONT COVERS IN LOWER L/H CORNER.
- 5) INSTALLATION INSTRUCTION SHEET INCLUDED

1-5-07	REV PER 2006-177 CJD
03/27/03	ADDED X4392 SAFETY GUIDE (8) JMS
4-6-01	ADD TUBE INSUL TO 5-TERM BUS TC
3-20-97	ADDED INSTRUC SHEET TC

UNLESS OTHERWISE SPECIFIED  
DIMENSIONS ARE IN INCHES  
TOLERANCES:

.XX  
.XXX  
HOLE DIAMETER  
ANGULAR  
UNDIMENSIONED 90° ANGLES

DWN	JO	DATE	2-11-97
CHK		DATE	
APVD		DATE	

-CONFIDENTIAL-PROPERTY OF  
**Siemens Energy & Automation, Inc.**  
Residential Products Division

MTR SKT 4 POS 100A 5T VERT

SIZE	ISSUE RELEASE NO.	DWG NO.	REV
B		UVS410	
SCALE	DO NOT SCALE DRAWING	SHEET	1 OF 1