



NOTES:

- 1) FINISH: GRAY
- 2) CABINET: 16GA CRS
- 3) 100 AMP CONTINUOUS PER POSITION
300 VAC, 1 PHASE, 3 WIRE
240 AMP (TOTAL) UNIT RATING COPPER
200 AMP (TOTAL) UNIT RATING ALUMINIUM
- 4) CAT# LABEL ON FRONT COVERS IN LOWER L/H CORNER.
- 5) INSTALLATION INSTRUCTION SHEET INCLUDED

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES:
.XX
.XXX

HOLE DIAMETER
ANGULAR
UNDIMENSIONED 90° ANGLES

DWN	JO	DATE	2-12-97
CHK		DATE	
APVD		DATE	

1-5-07	REV PER 2006-177 CJD
03/27/03	ADDED X4392 SAFETY GUIDE (6) JMS
4-10-01	ADD TUBE INSUL TO 5-TERM BUS TC
3-20-97	ADDED INSTRUC SHEET TC

-CONFIDENTIAL-PROPERTY OF
Siemens Energy & Automation, Inc.
Residential Products Division

MTR SKT 4 POS 100A 5T VERT 1 BLANK

SIZE	ISSUE RELEASE NO.	DWG NO.	REV
B		UVS411B	
SCALE	DO NOT SCALE DRAWING	SHEET	1 OF 1