

SIEMENS

3B3M300CD16 - Three-Phase Ventilated-USA-DOE


PRODUCT DETAILS			
KVA:	300.00	Enclosure:	NEMA 3R Ventilated
UPC#:		Phase:	Three-Phase
Line Voltage	208V-Delta	Load Voltage	208Y/120V
E/S Shielded:	No	Windings:	Copper
Temp. rise:	150°	Hertz:	60 Hz
Taps:	1 - 5% FCAN; 2 - 5% FCBN	Approvals:	UL, cUL, DOE
		Wall Bracket:	n/a
WEIGHT AND DIMENSIONS			
Height(A):	46.00"	Width(B):	35.00"
Depth(C):	37.00"	Shipping Weight:	1935 lbs
ADDITIONAL INFORMATION			
How to Buy: Contact Siemens Distributor, Siemens Sales Rep or Configure in COMPAS Configuration Tool			

Wiring Diagram

T208F Wiring Diagram & Connections*

Wiring Diagram

Primary: 208 Volts Delta
Secondary: 208Y/120 Volts



Connections

Primary Volts	On Each Coil Jumper Taps To	Primary Lines Connect To
218	1	H1, H2, H3
208	2	H1, H2, H3
198	3	H1, H2, H3
187	4	H1, H2, H3
Sec. Volts	Secondary Lines Connect To	
208	X1, X2, X3	
120	Between X0 and X1 or X2 or X3	
1 Phase		

Dimensional Drawing

Figure 24

