



# Pushbutton Units and Indicator Lights

## Class 51, Hazardous Location NEMA Type 7 & 9 Devices

### Indicator lights

#### Selection and ordering data

Version	Color of actuator	Contacts	Short bushing order No.	Long bushing order No.	Weight approx. lbs.	Pack Unit
<b>Indicator light - full voltage</b> 	<b>Indicator light with glass lens - Full voltage type AC/DC (with 6" pigtail leads) <sup>1) 3)</sup></b>					
	Operators with Incandescent Lamp	Red		51PC5B2	51PC5B2LB	1
	6-8V with 755 type	Green		51PC5B3	51PC5B3LB	1
		Amber		51PC5B9	51PC5B9LB	1
		Less lens		51PC5BN	51PC5BNLB	1
	12V with 756 type	Red		51PC5C2	51PC5C2LB	1
		Amber		51PC5C3	51PC5C3LB	1
		Green		51PC5C9	51PC5C9LB	1
		Less lens		51PC5CN	51PC5CNLB	1
	24V with 757 type	Red		51PC5D2	51PC5D2LB	1
		Green		51PC5D3	51PC5D3LB	1
		Amber		51PC5D9	51PC5D9LB	1
		Less lens		51PC5DN	51PC5DNLB	1
	Operators with LED Lamp <sup>2)</sup>	Red		51PE5B2	51PE5B2LB	1
	6-8V with BA9 type LED	Green		51PE5B3	51PE5B3LB	1
		Amber		51PE5B9	51PE5B9LB	1
12V with BA9 type LED	Red		51PE5C2	51PE5C2LB	1	
			51PE5C3	51PE5C3LB	1	
			51PE5C9	51PE5C9LB	1	
24V with BA9 type LED	Red		51PE5D2	51PE5D2LB	1	
	Green		51PE5D3	51PE5D3LB	1	
	Amber		51PE5D9	51PE5D9LB	1	
<b>Indicator light - transformer type</b> 	<b>Indicator light with glass lens - Transformer type AC/DC <sup>1) 3)</sup></b>					
	Operators with Incandescent Lamp	Red		51PC5G2	51PC5G2LB	1
	120V with 6V 755 type lamp	Green		51PC5G3	51PC5G3LB	1
		Amber		51PC5G9	51PC5G9LB	1
		Less lens		51PC5GN	51PC5GNLB	1
	240V with 6V 755 type lamp	Red		51PC5H2	51PC5H2LB	1
		Green		51PC5H3	51PC5H3LB	1
		Amber		51PC5H9	51PC5H9LB	1
		Less lens		51PC5HN	51PC5HNLB	1
	480V with 6V 755 type lamp	Red		51PC5J2	51PC5J2LB	1
		Green		51PC5J3	51PC5J3LB	1
		Amber		51PC5J9	51PC5J9LB	1
		Less lens		51PC5JN	51PC5JNLB	1
	600V with 6V 755 type lamp	Red		51PC5K2	51PC5K2LB	1
		Green		51PC5K3	51PC5K3LB	1
		Amber		51PC5K9	51PC5K9LB	1
		Less lens		51PC5KN	51PC5KNLB	1
	Operators with LED Lamp <sup>2)</sup>	Red		51PE5G2	51PE5G2LB	1
	120V with 6V BA9 type LED	Green		51PE5G3	51PE5G3LB	1
		Amber		51PE5G9	51PE5G9LB	1
		Less lens		—	—	1
	240V with 6V BA9 type LED	Red		51PE5H2	51PE5H2LB	1
		Green		51PE5H3	51PE5H3LB	1
		Amber		51PE5H9	51PE5H9LB	1
	Less lens		—	—	1	
480V with 6V BA9 type LED	Red		51PE5J2	51PE5J3LB	1	
	Green		51PE5K3	51PE5K3LB	1	
	Amber		51PE5K9	51PE5K9LB	1	
	Less lens		—	—	1	
600V with 6V BA9 type LED	Red		51PE5T2	51PE5T2LB	1	
	Green		51PE5T3	51PE5T3LB	1	
	Amber		51PE5T9	51PE5T9LB	1	
	Less lens		—	—	1	
<b>Indicator light with plastic lens - Resistor type AC/DC*</b>	Red		51PC5M2	51PC5M2LB	1	
	Green		51PC5M3	51PC5M3LB	1	
	Amber		51PC5M9	51PC5M9LB	1	
	Less lens		51PC5MN	51PC5MNLB	1	
	120V with 24V BA9 type LED lamp <sup>2)</sup>	Red		51PE5N2	51PE5N2LB	1
		Green		51PE5N3	51PE5N3LB	1
	Amber		51PE5N9	51PE5N9LB	1	

1) For other colors not listed, order operator less lens and separate lens from page 10/101.

2) LED color must match lens color.

3) All illuminated devices come with std. Touch-safe shield per UL stds.