



Pushbutton Units and Indicator Lights

Class 51, Hazardous Location NEMA Type 7 & 9 Devices

Selector switch operators

Selection and ordering data

Version	Lever type	Color of insert	Cam Code ^{1) 2)}	Short bushing order No.	Long bushing order No.	Weight approx.	Pack
						lbs.	Unit
	Short lever, non-Illuminated	White	A	51SA2AA	51SA2AALB		1
	Long lever, non-Illuminated	White	A	51SB2AA	51SB2AALB		
Spring return from right operation	Short lever, non-Illuminated	White	A	51SA2AC	51SA2ACLB		1
	Long lever, non-Illuminated	White	A	51SB2AC	51SB2ACLB		
	Short lever, non-Illuminated	White	B	51SA2BA	51SA2BALB		1
	Long lever, non-Illuminated	White	B	51SB2BA	51SB2BALB		
	Short lever, non-Illuminated	White	C	51SA2CA	51SA2CALB		
	Long lever, non-Illuminated	White	C	51SB2CA	51SB2CALB		
	Short lever, non-Illuminated	White	D	51SA2DA	51SA2DALB		
	Long lever, non-Illuminated	White	D	51SB2DA	51SB2DALB		
	Short lever, non-Illuminated	White	E	51SA2EA	51SA2EALB		
	Long lever, non-Illuminated	White	E	51SB2EA	51SB2EALB		
	Short lever, non-Illuminated	White	G	51SA2GA	51SA2GALB		
	Long lever, non-Illuminated	White	G	51SB2GA	51SB2GALB		
Spring return from right operation	Short lever, non-Illuminated	White	B	51SA2BC	51SA2BCLB		1
	Long lever, non-Illuminated	White	B	51SB2BC	51SB2BCLB		
	Short lever, non-Illuminated	White	C	51SA2CC	51SA2CCLB		
	Long lever, non-Illuminated	White	C	51SB2CC	51SB2CCLB		
	Short lever, non-Illuminated	White	D	51SA2DC	51SA2DCLB		
	Long lever, non-Illuminated	White	D	51SB2DC	51SB2DCLB		
	Short lever, non-Illuminated	White	E	51SA2EC	51SA2ECLB		
	Long lever, non-Illuminated	White	E	51SB2EC	51SB2ECLB		
	Short lever, non-Illuminated	White	G	51SA2GC	51SA2GCLB		
	Long lever, non-Illuminated	White	G	51SB2GC	51SB2GCLB		
Spring return from left operation	Short lever, non-Illuminated	White	B	51SA2BB	51SA2BBLB		1
	Long lever, non-Illuminated	White	B	51SB2BB	51SB2BBLB		
	Short lever, non-Illuminated	White	C	51SA2CB	51SA2CBLB		
	Long lever, non-Illuminated	White	C	51SB2CB	51SB2CBLB		
	Short lever, non-Illuminated	White	D	51SA2DB	51SA2DBLB		
	Long lever, non-Illuminated	White	D	51SB2DB	51SB2DBLB		
	Short lever, non-Illuminated	White	E	51SA2EB	51SA2EBLB		
	Long lever, non-Illuminated	White	E	51SB2EB	51SB2EBLB		
	Short lever, non-Illuminated	White	G	51SA2GB	51SA2GBLB		
	Long lever, non-Illuminated	White	G	51SB2GB	51SB2GBLB		
Spring return from left and right operation	Short lever, non-Illuminated	White	B	51SA2BD	51SA2BDLB		1
	Long lever, non-Illuminated	White	B	51SB2BD	51SB2BDLB		
	Short lever, non-Illuminated	White	C	51SA2CD	51SA2CDLB		
	Long lever, non-Illuminated	White	C	51SB2CD	51SB2CDLB		
	Short lever, non-Illuminated	White	D	51SA2DD	51SA2DDLb		
	Long lever, non-Illuminated	White	D	51SB2DD	51SB2DDLb		
	Short lever, non-Illuminated	White	E	51SA2ED	51SA2EDLB		
	Long lever, non-Illuminated	White	E	51SB2ED	51SB2EDLB		
	Short lever, non-Illuminated	White	G	51SA2GD	51SA2GDLb		
	Long lever, non-Illuminated	White	G	51SB2GD	51SB2GDLb		

1) C cam limited to 4 single or double pole blocks on spring return operators.

2) For contact operation, see cam selection chart on page 10/99.