

# Pushbutton Units and Indicator Lights

## Class 51, Hazardous Location NEMA Type 7 & 9 Devices

### Selector switch operators

#### Selection and ordering data



Version	Key removal position	Lock number	Cam Code <sup>1) 2)</sup>	Short bushing order No.	Long bushing order No.	Weight approx.		Pack	
						lbs.	Unit		
<b>Key-operated selector switches with 2 switching positions</b>	Both	550CH	A	<b>51SA6AE</b>	<b>51SA6AELB</b>			1	
	Left	550CH	A	<b>51SA6AF</b>	<b>51SA6AFLB</b>				
Maintained operation									
Spring return from right operation	Left	550CH	A	<b>51SA6AC</b>	<b>51SA6ACLB</b>			1	
<b>Key-operated selector switches with 3 switching positions</b>	All	550CH	B	<b>51SA6BE</b>	<b>51SA6BELB</b>			1	
			C	<b>51SA6CE</b>	<b>51SA6CELB</b>				
Maintained operation									
Left	550CH	B	D	<b>51SA6DE</b>	<b>51SA6DELB</b>			1	
			E	<b>51SA6EE</b>	<b>51SA6EELB</b>				
			G	<b>51SA6GE</b>	<b>51SA6GELB</b>				
			C	<b>51SA6CF</b>	<b>51SA6CFLB</b>				
Right	550CH	B	D	<b>51SA6DF</b>	<b>51SA6DFLB</b>			1	
			E	<b>51SA6EF</b>	<b>51SA6EFLB</b>				
			G	<b>51SA6GF</b>	<b>51SA6GFLB</b>				
			C	<b>51SA6CG</b>	<b>51SA6CGLB</b>				
Center	550CH	B	D	<b>51SA6DG</b>	<b>51SA6DGLB</b>			1	
			E	<b>51SA6EG</b>	<b>51SA6EGLB</b>				
			G	<b>51SA6GG</b>	<b>51SA6GGLB</b>				
			C	<b>51SA6CH</b>	<b>51SA6CHLB</b>				
Left and Center	550CH	B	D	<b>51SA6DH</b>	<b>51SA6DHLB</b>			1	
			E	<b>51SA6EH</b>	<b>51SA6EHLB</b>				
			G	<b>51SA6GH</b>	<b>51SA6GHLB</b>				
			C	<b>51SA6CK</b>	<b>51SA6CKLB</b>				
Spring return from right operation	Center	550CH	B	<b>51SA6BK</b>	<b>51SA6BKLB</b>			1	
			C	<b>51SA6CK</b>	<b>51SA6CKLB</b>				
			D	<b>51SA6DK</b>	<b>51SA6DKLB</b>				
			E	<b>51SA6EK</b>	<b>51SA6EKLb</b>				
Spring return from left operation	Center	550CH	B	<b>51SA6BU</b>	<b>51SA6BULB</b>			1	
			C	<b>51SA6CU</b>	<b>51SA6CULB</b>				
			D	<b>51SA6DU</b>	<b>51SA6DULB</b>				
			E	<b>51SA6EU</b>	<b>51SA6EULB</b>				
Spring return from left and right operation	Center	550CH	B	<b>51SA6GU</b>	<b>51SA6GULB</b>			1	
			C	<b>51SA6CV</b>	<b>51SA6CVLB</b>				
			D	<b>51SA6DV</b>	<b>51SA6DVLB</b>				
			E	<b>51SA6EV</b>	<b>51SA6EVLB</b>				
Lock types keyed different from standard - up to 25 per order				B	<b>51SA6BV</b>	<b>51SA6BVLB</b>		1	
				C	<b>51SA6CV</b>	<b>51SA6CVLB</b>			
				D	<b>51SA6DV</b>	<b>51SA6DVLB</b>			
				E	<b>51SA6EV</b>	<b>51SA6EVLB</b>			

5

5

To order special locks for keyed selector switches, append corresponding 'X' suffix to part number

Ordering example:	#549CH	X639	1
51SA6AEX298	#548CH	X640	1
	#547CH	X641	1
	#501CH	X642	1
	#506CH	X643	1

1) C cam limited to 4 single or double pole blocks on spring return operators.

2) For contact operation, see cam selection chart on page 10/99.