

DISTRIBUTION WIRE CONNECTOR 6 CABLES 3 PCS.
ACCESSORY FOR: 3VA5 250



Model	
Product brand name	SETRON
Product designation	accessories

Connections according IEC	
Connectable conductor cross-section	
<ul style="list-style-type: none"> • for copper cable / solid / minimum • for copper cable / solid / maximum • for copper cable / finely stranded / minimum • for copper cable / finely stranded / maximum • for copper cable / stranded / minimum • for copper cable / stranded / maximum • for aluminum cable / solid / minimum • for aluminum cable / solid / maximum • for aluminum cable / stranded / minimum • for aluminum cable / stranded / maximum 	<ul style="list-style-type: none"> 1.5 mm² 16 mm² 1.5 mm² 25 mm² 1.5 mm² 35 mm² 4 mm² 16 mm² 4 mm² 35 mm²
Wire stripping length	14,4 / 26 / 38,5 mm
Tightening torque / when using copper cables	
<ul style="list-style-type: none"> • solid 	<= 10 mm ² : 6.2 Nm, > 10 mm ² : 7 Nm

- stranded
- finely stranded






<= 10 mm²: 6.2 Nm, > 10 mm²: 7 Nm

<= 10 mm²: 6.2 Nm, > 10 mm²: 7 Nm

Connections according UL

Wire stripping length	0.6 / 1.0 / 1.5 in
Connectable conductor cross-section	
<ul style="list-style-type: none"> • for copper cable / solid / minimum • for copper cable / solid / maximum • for copper cable / stranded / minimum • for copper cable / stranded / maximum • for copper cable / finely stranded / minimum • for copper cable / finely stranded / maximum • for aluminum cable / solid / minimum • for aluminum cable / solid / maximum • for aluminum cable / stranded / minimum • for aluminum cable / stranded / maximum 	14 AWG 10 AWG 14 AWG 2 AWG 14 AWG 2 AWG 12 AWG 10 AWG 12 AWG 2 AWG
Tightening torque / when using copper cables	
<ul style="list-style-type: none"> • solid • stranded • finely stranded 	<= 8 AWG: 55 lb-in, > 8 AWG: 65 lb-in <= 8 AWG: 55 lb-in, > 8 AWG: 65 lb-in <= 8 AWG: 55 lb-in, > 8 AWG: 65 lb-in

Certificates

General Product Approval	EMC	Declaration of Conformity	other
			
			Miscellaneous

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9233-0JF60>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9233-0JF60>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)







http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9233-0JF60

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

11/20/2017