

BOX TERMINAL 3 PCS. ACCESSORY FOR: 3VA6 400/600



Model	
Product brand name	SETRON
Product designation	accessories
Connections according IEC	
Connectable conductor cross-section	
<ul style="list-style-type: none"> <li>• for copper cable / finely stranded / minimum</li> </ul>	35 mm <sup>2</sup>
<ul style="list-style-type: none"> <li>• for copper cable / finely stranded / maximum</li> </ul>	240 mm <sup>2</sup>
<ul style="list-style-type: none"> <li>• for copper cable / stranded / minimum</li> </ul>	35 mm <sup>2</sup>
<ul style="list-style-type: none"> <li>• for copper cable / stranded / maximum</li> </ul>	300 mm <sup>2</sup>
Wire stripping length	26 mm
Tightening torque / when using copper cables	
<ul style="list-style-type: none"> <li>• stranded</li> </ul>	<= 95 mm <sup>2</sup> : 16 Nm, >= 120 mm <sup>2</sup> : 28 Nm
<ul style="list-style-type: none"> <li>• finely stranded</li> </ul>	<= 95 mm <sup>2</sup> : 16 Nm, >= 120 mm <sup>2</sup> : 28 Nm
Connections according UL	
Wire stripping length	1.0 in
Connectable conductor cross-section	
<ul style="list-style-type: none"> <li>• for copper cable / stranded / minimum</li> </ul>	1/0 AWG
<ul style="list-style-type: none"> <li>• for copper cable / stranded / maximum</li> </ul>	500 kcmil

<ul style="list-style-type: none"> <li>• for copper cable / finely stranded / minimum</li> <li>• for copper cable / finely stranded / maximum</li> </ul>	<p>1/0 AWG</p> <p>500 kcmil</p>
<p>Tightening torque / when using copper cables</p> <ul style="list-style-type: none"> <li>• stranded</li> <li>• finely stranded</li> </ul>	<p>&lt;= 4/0 AWG: 140 lb-in, &gt;= 250 kcmil: 250 lb-in</p> <p>&lt;= 4/0 AWG: 140 lb-in, &gt;= 250 kcmil: 250 lb-in</p>

### Certificates

General Product Approval	EMC	Declaration of Conformity	other
--------------------------	-----	---------------------------	-------



[Miscellaneous](#)

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9473-0JA13>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9473-0JA13>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**



[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3VA9473-0JA13](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9473-0JA13)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



**last modified:**

11/20/2017