



REVISION	DATE	BY	DATE	BY
		DRAWN	06/03/15	CY
		CHEK'D		
		VERIF'D		


Confidential - Property of <b>Siemens Industry, Inc.</b> Building Technologies Division		
CUSTOMER		
ORDER NO.	DWG. NO.	
	1D1Y015TP1	SH 1 OF 2

# SIEMENS


CATALOG NO. 1D1Y015TP1 SERIAL NO. <b>15</b> kVA <b>60</b> Hz    1 PHASE <b>6</b> % IMP AT 170 °C <b>150</b> °C RISE    °C AVG. AMBIENT <b>220</b> °C TEMP CLASS    °C MAX. AMBIENT PRIMARY ( H1 H3 H2 H4 ) 240X480V V SECONDARY(X4 X2 X3 X1 ) 120/240V V WINDING MATERIAL AL ENCLOSURE TYPE NEMA-3R WEIGHT 175 LBS ENERGY EFFICIENCY NEMA TP 1-2002	SERIES H LISTED DISTRIBUTION TRANSFORMER 77US TYPE F  LR 3902 E112313 SUITABLE FOR INDOOR OR OUTDOOR LOCATIONS DO NOT INSTALL IN AREAS ACCESSIBLE TO PUBLIC FOR INSTALLATION SEE INSTRUCTION MANUAL NEMA Class ANN Dry Type Transformer Siemens Industry, Inc. Norcross, GA
	



FRONT VIEW



SIDE VIEW



All Dimensions in inches

ENCLOSURE COLOR : ANSI 61 GREY – OUTDOOR

CUSTOMER NOTES:

- HV1 TERMINATED AT TOP FRONT
- LV1 TERMINATED AT BOTTOM FRONT

Confidential – Property of  
**Siemens Industry, Inc.**  
 Building Technologies Division

REVISION	DATE	BY	DATE	BY
		DRAWN	06/03/15	CY
		CHEK'D		
		VERIF'D		

CUSTOMER	
ORDER NO.	DWG. NO. 1D1Y015TP1
SH 2 OF 2	

0.2 j.wen 2010/01/21 13:27