



REVISION	DATE	BY	DATE	BY
		DRAWN	05/07/13	GR
		CHEK'D		
1	06/01/04	GR	VERIF'D	

HCN: 25568


SIEMENS

CATALOG NO. 1D1Y025CTP1 SERIAL NO. SERIES H 25 kVA 60 Hz 1 PHASE 5.6 % IMP AT 170 °C		°C AVG. AMBIENT °C MAX. AMBIENT PRIMARY (H1 H3 H2 H4) 240X480V V SECONDARY(X4 X2 X3 X1) 120/240V V	
WINDING MATERIAL CU ENCLOSURE TYPE NEMA-3R WEIGHT 295 LBS ENERGY EFFICIENCY NEMA TP 1-2002		LISTED DISTRIBUTION TRANSFORMER 77US TYPE F  LR 3902 E112313	
MEETS TP-1 EFFICIENCY REQUIREMENTS SUITABLE FOR INDOOR OR OUTDOOR LOCATIONS DO NOT INSTALL IN AREAS ACCESSIBLE TO PUBLIC FOR INSTALLATION SEE INSTRUCTION MANUAL NEMA Class ANN Dry Type Transformer Siemens Industry, Inc. Norcross, GA			



Confidential - Property of Siemens Industry, Inc. Building Technologies Division		
CUSTOMER		
ORDER NO.	DWG. NO.	1
	1D1Y025CTP1	SH 1 OF 2

dsu0082e1



All Dimensions in inches

ENCLOSURE COLOR : ANSI 61 GREY – OUTDOOR

H.V.1. TERMINAL DETAIL

L.V.1. TERMINAL DETAIL

MECHANICAL TYPE LUGS INCLUDED
SUITABLE FOR #14-2 CU/AL
CONDUCTORS
1 CONDUCTOR PER PHASE

MECHANICAL TYPE LUGS INCLUDED
SUITABLE FOR #2/0-6 CU/AL
CONDUCTORS
1 CONDUCTOR PER PHASE

CUSTOMER NOTES:

- HV1 TERMINATED AT TOP FRONT
- LV1 TERMINATED AT BOTTOM FRONT

Confidential – Property of
Siemens Industry, Inc.
Building Technologies Division

REVISION	DATE	BY	DATE	BY	CUSTOMER
			05/07/13	GR	
1	06/01/04	GR			
					ORDER NO.
					DWG. NO.
					1
					1D1Y025CTP1
					SH 2 OF 2

1.1 Jwen 2010/01/21 13:27