



Features and Ratings

- Ringless Type Meter Socket
- 250A Continuous, 200A Per position, 600V AC
- Outdoor Enclosure (NEMA Type 3R)
- Painted G90 Steel
- 1 Phase, 3 Wire
- 4 Jaw Meter Socket
- For Underground Service

Connectors, Wire Sizes and Torques

CONNECTOR	WIRE SIZE	TORQUE
LINE, LOAD & NEUTRAL	#6-350kcmil	375 IN.-LBS.
GROUND	#14-1/0 AWG	50 IN.-LBS.



© 2015 Copyright Siemens Industry, Inc.



Rainproof Combination Metering

Description:

2 SKT/PED 200A 1P FM/DB

2/17/05 JT

DO NOT SCALE DRAWING

Dwg No:

UAP2317-PPWI