



MATERIAL:

Dimensions in millimetres : Surface texture in micrometres. Machine where marked ✓
 For explanation of dimensions, tolerances, notes etc. see B.S.308.
 Limit on untoleranced unmachined dimensions ± _____
 Limits on untoleranced machined dimensions to B.S.4500;
 i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;
 over 6 to 30±0.2; over 120 to 315±0.5;
 General unmachined angular tolerance ± _____

Finish: _____
 Treatment: _____

Title: TYPICAL SCHEME DIAGRAM FOR 2 PHASE (DIR) + SEF. DCD OVERCURRENT RELAY

Reyrolle Protection Hebburn.

Original Scale: NTS

First used on: _____
 Similar Articles: 2434W10037
 Supersedes: _____
 Drg. No. **2434W10022**

2	16/10/97	MN434/103
1	16/10/97	CHANGE NOTED
ISSUE	DATE	NOTED

