



**NOT SUBJECT TO UPDATE
ONCE COPIED / PRINTED
OR DOWNLOADED**

- NOTES
- 1 CT CIRCUITS ARE SHOWN CONNECTED TO RELAY 1 AMP TAP. USE ALTERNATIVE TAP FOR 5AMP RATED CTs.
 - 2 CT & EARTH CONNECTIONS ARE TYPICAL ONLY.
 - 3 FOR TERMINAL DIAGRAM SEE 2434W20003 (A2)
 - 4 DRG SHOWS OPTION B (11 O/P. 5 I/P).

MATERIAL:

Dimensions in millimetres : Surface texture in micrometres.
Machine where marked ✓
For explanation of dimensions, tolerances, notes etc. see B.S.308.
Limit on untoleranced unmachined dimensions ± _____
Limits on untoleranced machined dimensions to B.S.4500;
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;
over 6 to 30±0.2; over 120 to 315±0.5;
General unmachined angular tolerance ± _____

Finish: _____

Title:
TYPICAL SCHEME DIAGRAM FOR 2 PHASE (DIR) + E/F (DIR)
DCD OVERCURRENT RELAY

First used on:
Similar Articles: 2434W10038
Supersedes:

Treatment: _____

**Reyrolle Protection
Hebburn.**

Original Scale:
NTS

Dr. No.
2434W10023

2	20/10/97	MN434/103
1	16/10/97	CHANGE NOTED

Copyright © Reyrolle Ltd.

ISSUE DATE NOTED