



NOTES

- 1 CT CIRCUITS ARE SHOWN CONNECTED TO RELAY 1 AMP TAP. USE ALTERNATIVE TAP FOR 5AMP RATED CTs.
- 2 CT & EARTH CONNECTIONS ARE TYPICAL ONLY.
- 3 FOR TERMINAL DIAGRAM SEE 2434W20003 (A2)
- 4 DRG SHOWS OPTION C (7 O/P. 9 I/P)

NOT SUBJECT TO UPDATE
ONCE COPIED / PRINTED
OR DOWNLOADED

MATERIAL:

Dimensions in millimetres : Surface texture in micrometres.
Machine where marked ✓
For explanation of dimensions, tolerances, notes etc. see B.S.308.
Limit on untoleranced unmachined dimensions ± _____
Limits on untoleranced machined dimensions to B.S.4500;
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;
over 6 to 30±0.2; over 120 to 315±0.5;
General unmachined angular tolerance ± _____

Finish: _____
Treatment: _____

Title: TYPICAL SCHEME DIAGRAM FOR 2 PHASE (DIR) + E/F (DIR).
DCD OVERCURRENT RELAY

Reyrolle Protection
Hebburn.

Original Scale: NTS

First used on: _____
Similar Articles: 2434W10023
Supersedes: _____
Drg. No. 2434W10038

1	16/10/97	CHANGE NOTED	△
ISSUE	DATE		

Copyright © Reyrolle Ltd.