



<p>MATERIAL:</p> <p>Dimensions in millimetres : Surface texture in micrometres. Machine where marked ✓ For explanation of dimensions, tolerances, notes etc. see B.S.308. Limit on untoleranced unmachined dimensions ± _____ Limits on untoleranced machined dimensions to B.S.4500; i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8; over 6 to 30±0.2; over 120 to 315±0.5; General unmachined angular tolerance ± _____</p>	<p>Finish: _____</p> <p>Treatment: _____</p>	<p>Title: TYPICAL SCHEME FOR 2 PH DIR + CURRENT POL DIR E/F & 3 PH DIR + CURRENT POL DIR E/F DCD RELAY</p> <p style="font-size: 1.2em; font-weight: bold; text-align: center;">Reyrolle Protection Hebburn.</p> <p>Original Scale: NTS</p>	<p>1 ISSUE</p>	<p>20/10/97 DATE</p>	<p>CHANGE NOTED</p>
<p>First used on: _____</p> <p>Similar Articles: 2434W10043</p> <p>Supersedes: _____</p> <p>Dr. No. 2434W10043</p>			<p>Copyright © Reyrolle Ltd.</p>		