



|   |  |             |  |   |  |                              |  |
|---|--|-------------|--|---|--|------------------------------|--|
| <b>MATERIAL:</b>  |  | Finish:     |  | Title:  |  | First used on:               |  |
| Dimensions in millimetres : Surface texture in micrometres. Machine where marked ✓<br>For explanation of dimensions, tolerances, notes etc. see B.S.308.<br>Limit on untoleranced unmachined dimensions ± _____<br>Limits on untoleranced machined dimensions to B.S.4500;<br>i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;<br>over 6 to 30±0.2; over 120 to 315±0.5;<br>General unmachined angular tolerance ± _____ |  | Treatment:  |  | TYPICAL SCHEMATIC DIAGRAM 2 PHASE (DIR) + E/F (DIR)<br>NUMERIC OVERCURRENT PROTECTION (ARGUS 2) EPSILON |  | Similar Articles: 2434W10038 |  |
| DRAWN M LEASK   |  | CHECKED     |  | APPROVED R.D.WATSON   |  | Supersedes:                  |  |
| DATE 23/07/02   |  | IE          |  | OPS   |  | Drg. No. 2434W10068          |  |
| PCP   |  | Purch.Spec. |  | TQ  |  | Original Scale. NTS          |  |
| EAC   |  | CE          |  | STD   |  | A3                           |  |

|       |          |              |
|-------|----------|--------------|
| 2     | 19/4/02  | MN434/2292   |
| 1     | 22/11/99 | CHANGE NOTED |
| ISSUE | DATE     | NOTED        |

Copyright © 1999 Reyrolle Ltd.