



MATERIAL:

Dimensions in millimetres : Surface texture in micrometres.  
Machine where marked ✓  
For explanation of dimensions, tolerances, notes etc. see B.S.308.  
Limit on untoleranced unmachined dimensions ± \_\_\_\_\_  
Limits on untoleranced machined dimensions to B.S.4500;  
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;  
over 6 to 30±0.2; over 120 to 315±0.5;  
General unmachined angular tolerance ± \_\_\_\_\_

Finish:

Treatment:

Title:

TYPICAL SCHEME DIAGRAM 2 PHASE + (E/F DIRECTIONAL)  
NUMERIC OVERCURRENT PROTECTION (ARGUS 2) EPSILON

**Reyrolle Protection  
Hebburn.**

Original Scale.

NTS

First used on:

Similar Articles: 2434W10039

Supersedes:

Drq. No.

2434W10070

DRAWN M LEASK    CHECKED    APPROVED R.D.WATSON    DATE 23/07/02    IE    OPS    PCP    Purch.Spec. TQ    EAC    CE    STD    A3

2	19/4/02	MN434/2292
1	22/11/99	CHANGE NOTED
ISSUE	DATE	NOTED

Copyright © 1999 Reyrolle Ltd.