



MATERIAL:

Dimensions in millimetres : Surface texture in micrometres.
Machine where marked ✓
For explanation of dimensions, tolerances, notes etc. see B.S.308.
Limit on untoleranced unmachined dimensions ± _____
Limits on untoleranced machined dimensions to B.S.4500;
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;
over 6 to 30±0.2; over 120 to 315±0.5;
General unmachined angular tolerance ± _____

Finish:

Treatment:

Title:
TYPICAL SCHEME DIAGRAM 3 PHASE + (DIRECTIONAL E/F)
NUMERIC OVERCURRENT PROTECTION (ARGUS 2) EPSILON

**Reyrolle Protection
Hebburn.**

Original Scale.
NTS

First used on:
Similar Articles: 2434W10042
Supersedes:

Dr. No.
2434W10076