



MATERIAL:

Dimensions in millimetres : Surface texture in micrometres.  
Machine where marked ✓  
For explanation of dimensions, tolerances, notes etc. see B.S.308.  
Limit on untoleranced unmachined dimensions ± \_\_\_\_\_  
Limits on untoleranced machined dimensions to B.S.4500;  
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;  
over 6 to 30±0.2; over 120 to 315±0.5;  
General unmachined angular tolerance ± \_\_\_\_\_

Finish:

Treatment:

Title:  
TYPICAL SCHEMATIC DIAGRAM 2 PHASE (DIR)+E/F (DIR)+SEF  
NUMERIC OVERCURRENT PROTECTION (ARGUS 2) EPSILON

Reyrolle Protection  
Hebburn.

Original Scale.  
NTS

First used on:  
Similar Articles: 2434W10077  
Supersedes:

Dr. No.  
2434W10078