



MATERIAL: Dimensions in millimetres : Surface texture in micrometres. Machine where marked ✓ For explanation of dimensions, tolerances, notes etc. see B.S.308. Limit on untoleranced unmachined dimensions ± _____ Limits on untoleranced machined dimensions to B.S.4500; i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8; over 6 to 30±0.2; over 120 to 315±0.5; General unmachined angular tolerance ± _____		Finish: _____ Treatment: _____	Title: ARGUS 2 DIGITAL DIRECTIONAL RELAY TYPICAL SCHEME DIAGRAM FOR 2P DIRECTIONAL P/F, 1P DIRECTIONAL E/F & 1P SEF RELAY WITH OPEN DELTA CONNECTED VT	First used on: _____ Similar Articles: 2434W10097 Supersedes: _____
DRAWN M LEASK CHECKED M ELLIS APPROVED RD.WATSON		DATE 10/6/03 IE OPS PCP Purch.Spec. TQ	Original Scale: NTS	Drg. No. 2434W10096