



**MATERIAL:**

Dimensions in millimetres : Surface texture in micrometres.  
Machine where marked ✓  
For explanation of dimensions, tolerances, notes etc. see B.S.308.  
Limit on untoleranced unmachined dimensions ± \_\_\_\_\_  
Limits on untoleranced machined dimensions to B.S.4500;  
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;  
over 6 to 30±0.2; over 120 to 315±0.5;  
General unmachined angular tolerance ± \_\_\_\_\_

Finish: \_\_\_\_\_

Title:  
TYPICAL SCHEME DIAGRAM FOR 3 PHASE (DIR) + SEF/REF  
NUMERIC OVERCURRENT PROTECTION (ARGUS 5&6) EPSILON

First used on:  
Similar Articles: 2716W10005  
Supersedes:

Treatment: \_\_\_\_\_

**Reyrolle Protection  
Hebburn.**

Original Scale:  
NTS

Drq. No.  
2716W10011

2	19/4/02	MN434/2292
1	22/11/99	CHANGE NOTED <span style="float: right;">△</span>
ISSUE	DATE	NOTED

Copyright © 1999 Reyrolle Ltd.