



<p>MATERIAL:</p> <p>Dimensions in millimetres : Surface texture in micrometres. Machine where marked ✓</p> <p>For explanation of dimensions, tolerances, notes etc. see B.S.308.</p> <p>Limit on untoleranced unmachined dimensions ± _____</p> <p>Limits on untoleranced machined dimensions to B.S.4500; i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8; over 6 to 30±0.2; over 120 to 315±0.5;</p> <p>General unmachined angular tolerance ± _____</p>	<p>Finish:</p> <hr/> <p>Treatment:</p>	<p>Title: TYPICAL SCHEME DIAGRAM FOR 3 PHASE DIRECTIONAL & E/F DIRECTIONAL OR 3 PHASE DIRECTIONAL & E/F NON DIRECTIONAL NUMERIC OVERCURRENT PROTECTION (ARGUS 5/6)</p> <p style="text-align: center; font-size: 1.2em; font-weight: bold;">Reyrolle Protection Hebburn.</p> <p style="text-align: right;">Original Scale: NTS</p>	<p>16/9/98</p> <p>16/9/98</p>	<p>1</p> <p>16/9/98</p>	<p>CHANGE NOTED</p> <p style="text-align: center;">△</p>							
<p>Dimensions in millimetres : Surface texture in micrometres. Machine where marked ✓</p> <p>For explanation of dimensions, tolerances, notes etc. see B.S.308.</p> <p>Limit on untoleranced unmachined dimensions ± _____</p> <p>Limits on untoleranced machined dimensions to B.S.4500; i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8; over 6 to 30±0.2; over 120 to 315±0.5;</p> <p>General unmachined angular tolerance ± _____</p>		<p>First used on:</p> <p>Similar Articles:</p> <p>Supersedes:</p>		<p>Drg. No.</p> <p style="font-size: 1.5em;">2716W10004</p>								
DRAWN M LEASK	CHECKED	APPROVED R.D.WATSON	DATE 24/07/02	IE	OPS	PCP	Purch.Spec.	TQ	EAC	CE	STD	A3