



NOT SUBJECT TO UPDATE  
ONCE COPIED / PRINTED  
OR DOWNLOADED

**MATERIAL:**

Dimensions in millimetres : Surface texture in micrometres.  
Machine where marked ✓  
For explanation of dimensions, tolerances, notes etc. see B.S.308.  
Limit on untoleranced unmachined dimensions ± \_\_\_\_\_  
Limits on untoleranced machined dimensions to B.S.4500;  
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;  
over 6 to 30±0.2; over 120 to 315±0.5;  
General unmachined angular tolerance ± \_\_\_\_\_

Finish: \_\_\_\_\_

Title: TYPICAL SCHEME DIAGRAM FOR 3 PHASE & DIRECTIONAL E/F  
NUMERIC OVERCURRENT PROTECTION (ARGUS 5/6)

First used on: \_\_\_\_\_

Treatment: \_\_\_\_\_

**Reyrolle Protection  
Hebburn.**

Original Scale:  
NTS

Similar Articles: \_\_\_\_\_

Supersedes: \_\_\_\_\_

Drq. No. **2716W10006**

DRAWN M LEASK	CHECKED	APPROVED R.D.WATSON	DATE 24/07/02	IE	OPS	PCP	Purch.Spec. TQ	EAC	CE	STD	A3
---------------	---------	---------------------	---------------	----	-----	-----	----------------	-----	----	-----	----

Copyright © Reyrolle Ltd. 16/9/98 CHANGE NOTED △