



MATERIAL: Dimensions in millimetres : Surface texture in micrometres. Machine where marked ✓ For explanation of dimensions, tolerances, notes etc. see B.S.308. Limit on untoleranced unmachined dimensions ± _____ Limits on untoleranced machined dimensions to B.S.4500; i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8; over 6 to 30±0.2; over 120 to 315±0.5; General unmachined angular tolerance ± _____		Finish: _____ Treatment: _____	Title: ARGUS 2 DIGITAL DIRECTIONAL RELAY TYPICAL SCHEME DIAGRAM FOR 3P DIRECTIONAL P/F & 1P DIRECTIONAL E/F RELAY WITH STAR CONNECTED VT VATECH REYROLLE AUTOMATION, CONTROL & PROTECTION	Original Scale: NTS	First used on: _____ Similar Articles: 2434W10089 Supersedes: _____ Drg. No. 2434W10089
DRAWN M LEASK CHECKED M ELLIS APPROVED RD. WATSON		DATE 9/6/03	IE OPS PCP Purch.Spec. TQ	EAC	CE STD A3

Copyright © 2002 VATECH REYROLLE ACP Ltd. Hebburn

1	11/12/02	CHANGE NOTED
ISSUE	DATE	NOTED