



<b>MATERIAL:</b> Dimensions in millimetres : Surface texture in micrometres. Machine where marked ✓ For explanation of dimensions, tolerances, notes etc. see B.S.308. Limit on untoleranced unmachined dimensions ± _____ Limits on untoleranced machined dimensions to B.S.4500; i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8; over 6 to 30±0.2; over 120 to 315±0.5; General unmachined angular tolerance ± _____		Finish: _____  Treatment: _____	<b>Title:</b> ARGUS 2 DIGITAL DIRECTIONAL RELAY TYPICAL SCHEME DIAGRAM FOR 2P DIRECTIONAL P/F, 1P DIRECTIONAL E/F & 1P SEF RELAY WITH STAR CONNECTED VT  <b>VATECH REYROLLE</b> <b>AUTOMATION, CONTROL &amp; PROTECTION</b>	Original Scale: NTS	First used on: _____ Similar Articles: 2434W10094 Supersedes: _____ Drg. No. <b>2434W10095</b>
DRAWN M LEASK    CHECKED M ELLIS    APPROVED RD.WATSON		DATE 9/6/03	IE    OPS    PCP    Purch.Spec. TQ	EAC	CE    STD    A3

Copyright © 2002 VATECH REYROLLE ACP Ltd. Hebburn

1	11/12/02	CHANGE NOTED
ISSUE	DATE	NOTED